

Switch disconnecter 3LD3, main switch 3-polig, Iu 40A operational switch at AC-23 A at 400 V 15,0 kW floor mounting Base mounting with door coupling center-hole 22,5 mm knob-operated mechanism black 48 x 48 mm



Model	
Product brand name	SENTRON
Product designation	3LD Switch disconnecter
Design of the product	Main switch
Display version / for switch position indicator manual operation	1 ON - 0 OFF
Design of the operating mechanism	selector switch
Design of handle	knob-operated mechanism, black
General technical data	
Number of poles	3
Type of device	fixed mounting
Type of switch	Floor mounting with door coupling
Operating frequency / maximum	50 1/h
Voltage	
Insulation voltage / rated value	690 V
Surge voltage resistance / rated value	6 kV
Protection class	
Protection class IP	IP65

Protection class IP / on the front	IP65
<b>Dissipation</b>	
<b>Power loss [W]</b>	2.5 W
<ul style="list-style-type: none"> <li>• for rated value of the current / at AC / in hot operating state / per pole</li> </ul>	
<b>Electricity</b>	
Current / at AC / rated value	40 A
Continuous current / rated value	40 A
Short-time current resistance (I <sub>cw</sub> ) / at 690 V / limited to 1 s / rated value	1 000 A
<b>Main circuit</b>	
<b>Operating frequency</b>	
<ul style="list-style-type: none"> <li>• initial value</li> </ul>	50 Hz
<ul style="list-style-type: none"> <li>• Full-scale value</li> </ul>	60 Hz
<b>Operating power</b>	
<ul style="list-style-type: none"> <li>• at AC-23 A / at 400 V / rated value</li> </ul>	18.5 kW
<ul style="list-style-type: none"> <li>• at AC-23 A / at 690 V / rated value</li> </ul>	15 kW
<ul style="list-style-type: none"> <li>• at AC-3 / at 400 V / rated value</li> </ul>	11.5 kW
<ul style="list-style-type: none"> <li>• at AC-3 / at 690 V / rated value</li> </ul>	11.5 kW
<b>Operating voltage</b>	
<ul style="list-style-type: none"> <li>• at AC / at 50/60 Hz / rated value</li> </ul>	690 V
<b>Auxiliary circuit</b>	
<b>Operating voltage / of auxiliary contacts / at AC / maximum</b>	500 V
<b>Continuous current / of the auxiliary contact / rated value</b>	10 A
<b>Insulation voltage / of the auxiliary switch / rated value</b>	500 V
<b>Suitability</b>	
<b>Suitability for use</b>	
<ul style="list-style-type: none"> <li>• Main switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• switch disconnecter</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• EMERGENCY OFF switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• safety switch</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• maintenance/repair switch</li> </ul>	Yes
<b>Product details</b>	
Product feature / interlock	Yes
Product extension / optional	
<ul style="list-style-type: none"> <li>• motor drive</li> </ul>	No
<ul style="list-style-type: none"> <li>• Voltage trigger</li> </ul>	No

Short-time current resistance (I <sub>cw</sub> ) / limited to 1 s / rated value	1 000 kA
Number of NC contacts	0
Number of NO contacts	0

### Connections

<b>Type of electrical connection</b>	Box terminal
<ul style="list-style-type: none"> <li>for main current circuit</li> </ul>	

### Requirements

<b>Design of the fuse link</b>	
<ul style="list-style-type: none"> <li>for short-circuit protection of the main circuit / required</li> </ul>	fuse gL/gG: 40 A
<ul style="list-style-type: none"> <li>for short-circuit protection of the auxiliary switch / required</li> </ul>	fuse gL/gG: 10 A

### Mechanical Design

<b>Height</b>	60 mm
<b>Width</b>	36 mm
<b>Depth</b>	380 mm
<b>Mounting type</b>	Built-in unit fixed-mounted version
<b>Mounting type</b>	
<ul style="list-style-type: none"> <li>front mounting with 4-hole attachment</li> </ul>	No
<ul style="list-style-type: none"> <li>front mounting with central attachment</li> </ul>	Yes
<ul style="list-style-type: none"> <li>rail mounting</li> </ul>	Yes
<b>Net weight</b>	300 g

### Environmental conditions

<b>Ambient temperature</b>	
<ul style="list-style-type: none"> <li>during operation / minimum</li> </ul>	-25 °C
<ul style="list-style-type: none"> <li>during operation / maximum</li> </ul>	55 °C

### Certificates

<b>Equipment marking</b>	
<ul style="list-style-type: none"> <li>acc. to DIN EN 61346-2</li> </ul>	S
<ul style="list-style-type: none"> <li>acc. to DIN EN 81346-2</li> </ul>	SF

### Declaration of Conformity



### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)  
<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3340-0TK11>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3LD3340-0TK11>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3LD3340-0TK11](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD3340-0TK11)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



