

KERN PCB 10000-1-2023e



The standard in the laboratory, ideal for a wide range of applications for Industry 4.0



Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,4 g
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g

Approval	
CE mark	✓

Display	
Display type	LCD
Display screen size	89×30 mm
Display backlight	✓
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction	
Dimension housing (W×D×H)	163×245×65 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	150×170 mm
Transport safety lock - bolt torque	0,4 Nm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	5
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 2 min 1 min 30 min 60 min 30 sec
PreTare function	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Rez A (Net total)

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PCB

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	10000 g
Readability [d]	0,1 g
Resolution	100.000
Linearity	± 0,3 g
Reproducibility	0,1 g
Default unit	g
Units	kg g gn dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa m
Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (F1)
Possible calibration points	2 kg; 5 kg; 10 kg
Stabilization time	3 s

KERN PCB 10000-1-2023e



The standard in the laboratory, ideal for a wide range of applications for Industry 4.0

Underfloor weighing	Hook (included in delivery)
Interfaces	RS-232 (optional) Bluetooth (optional) Ethernet (optional) USB-Device (optional) KUP WiFi (optional)
IP protection - display	no IP protection

Counting

Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, free, Input
Counting resolution (laboratory conditions)	50.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Battery	4×1.5 V AA
Battery / accumulator type	Li-Ion
Battery connection	Battery insert
Battery operating time	20 h

Environmental conditions

Humidity of environment [Max]	80 %
-------------------------------	------

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping


Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	235×365×175 mm
Net weight	1,4 kg
Shipping method	Parcel service
Net weight approx.	1,4 kg
Gross weight approx.	2,4 kg
Shipping weight	3 kg

Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

