

Product Data Sheet

MaxiFlex® Endurance™ 34-848

Colour – Coating	Black
Colour – Liner	Orange
Design	Palm coated knitwrist
Coating	NBR (Nitrile Butadiene Rubber)
Coating texture	Micro-Foam with Dots
Liner	Nylon, Spandex
Patent number	EP 1 608 808
Palm thickness	1.10 mm



Dimensions

Size Range	Size 5 (XXS)	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Total glove length (+/-10 mm)	185	195	210	220	225	230	235
Wrist length (mm)	55	55	55	60	65	65	65
Wrist width (mm)	65	65	65	70	70	70	75
Palm width (+/-3 mm)	78	82	84	90	97	100	104
Over lock colour	Purple	Blue	Red	Orange	White	Yellow	Black

EN test Results

Test	Notified Body	Result/Pass
EN 420: 2003 + A1: 2009	TÜV Rheinland	Yes
EN 388: 2016	TÜV Rheinland	4131A

If a glove due to its design and construction falls outside the scope of EN 420 in terms of hand size dimensions then this glove is classified as "fit for special purpose".



Product Data Sheet

MaxiFlex® Endurance™ 34-848

Typical Performance Values

EN 388:2016 A. Abrasion Resistance	> 8000 Cycles
EN 388:2016 B. Cut Resistance	> 1.2 index
EN 388:2016 C. Tear Resistance	> 50 newtons
EN 388:2016 D. Puncture Resistance	> 20 newtons
EN 388:2016 E. Cut Resistance ISO	≥ 2 Newton

HandCare®

Skin Health Alliance Dermatologically Accredited	Yes
REACH compliant	Yes
Oeko-Tex® 100	Certified
Sanitized®	Yes



Special features

Silicone free	No
---------------	----

Packaging

Pairs per poly bag	12
Carton count	144
Carton dimensions (mm)	500 x 295 x 270



Product Data Sheet

MaxiFlex® Endurance™ 34-848

Weight

Size Range	Size 5 (XXS)	Size 6 (XS)	Size 7 (S)	Size 8 (M)	Size 9 (L)	Size 10 (XL)	Size 11 (XXL)
Glove weight / Pair (+/- 6 gram)	24	26	30	38	40	42	44
Gross Weight (Kg)	4.8	5.1	5.7	6.8	7.1	7.4	7.7
Carton Weight (Kg)	1	1	1	1	1	1	1
Net Weight (Kg)	3.8	4.1	4.7	5.8	6.1	6.4	6.7

Issue date: 09.04.2018

