



TEGERA® 737

Synthetic glove, nitrile, double-dipped, nylon, 15 gg, sandy finish, Cat. II, black, blue, water and oil repellent, for fine assembly work

PROPERTIES

High level of protection, good fingertip sensitivity, flexible, very durable, excellent grip, good fit, comfortable, light

SPECIFICATION

TYPE OF GLOVE Work gloves - General handling

CATEGORY Cat. II

SIZE RANGE 7, 8, 9, 10, 11

LINER MATERIAL Nylon, 15 gg

DIPPING Double-dipped

DIPPING MATERIAL Nitrile

DEXTERITY 5

GRIP PATTERN Sandy finish

CUFF STYLE Knitwrist cuff

LENGTH RANGE 220 - 260 mm

COLOUR Black, blue

PAIRS PER PACKAGE/CARTON 12/120

DISPLAY Bag with euro slot


MATERIAL SPECIFICATION Nylon 49%, nitrile 50%, natural latex 1%

SIZE	ART. NO.	EAN NO.
7	737-7	7392626075061
8	737-8	7392626075078
9	737-9	7392626075085
10	737-10	7392626075047
11	737-11	7392626075054

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.



CE Cat. II



TEGERA® 737

FEATURES

Water and oil repellent, anatomically designed, soft, specially designed details

PRIMARY PROTECTION

Prevents risk of: abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt, contact with moisture, contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Slippery environments, oil and greasy environments, dirty environments

PRIMARY AREAS OF USE

Fine assembly, assembly, machine operating, building and construction, carpentry, painting, HVAC installation, construction, soil preparation, concrete work, engineering, mining, wood industry work, forest work, agricultural work, gardening, repair work, fishing industry work, paper industry work, decontamination, sanitation

PRIMARY INDUSTRIES OF USE

Agriculture, mining, oil, gas, petrochemical, pulp and paper, machinery and equipment, MRO, automotive, utilities, building and construction

TYPE OF WORK

Light weight

2(3)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2016-02-03

TEGERA® 737

EC TYPE EXAMINATION

Notified Body: 0362 Intertek ITS Testing Services Ltd,
Centre Court, Meridian Business Park, Leicester, LE19 1WD,
United Kingdom

COMPLIANCE DESCRIPTION


EN 420:2003 + A1:2009 Protective gloves - general requirements and test methods

EN 388:2003 Protective gloves against mechanical risks

Property	Level Achieved	(Maximum Performance)
A) Resistance to wear (No. of revolutions)	4	(4)
B) Resistance to cutting (Index)	1	(5)
C) Tear resistance (Newton)	3	(4)
D) Puncturing resistance (Newton)	1	(4)

EN 388 - Testing (specifies the requirements that apply for each safety level).

Level of protection	1	2	3	4	5
A) Resistance to wear (No. of revolutions)	100	500	2000	8000	
B) Resistance to cutting (Index)	1,2	2,5	5,0	10,0	20,0
C) Tear resistance (Newton)	10	25	50	75	
D) Puncturing resistance (Newton)	20	60	100	150	



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2016-02-03

3(3)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com