



## Laboratory Sample Kit Precision MELF Resistors MMA 0204-25 0.1 %



### FEATURES

- Resistors
  - Approved to EN 140401-803
  - AEC-Q200 qualified
  - Advanced thin film technology
  - Compliant to RoHS Directive 2002/95/EC



**RoHS**  
COMPLIANT

Files contain lengths of blister tape, each holding 20 resistors. The kit contains every fourth value of the E 96-series. Parts are sorted in the ascending order of its resistance value and appropriately marked.

SPECIFICATIONS	
Laboratory kit	LMA 96/4
Resistor type	MMA 0204-25 0.1 %
Temperature coefficient	± 25 ppm/K
Tolerance	± 0.1 %
Resistance range/E-series	43 Ω to 511 kΩ/every 4 <sup>th</sup> value of E 96 <sup>(1)</sup>
Number of resistance values	99
Resistors per value/total	20/1980
Number of pages/files	10/1

### Notes

- The products are specified by the underlying standard product's datasheet "Precision MELF Resistors" in its most current edition at [www.vishay.com/doc?28714](http://www.vishay.com/doc?28714)
- <sup>(1)</sup> Supplemented by 43R

PART NUMBER AND PRODUCT DESCRIPTION						
<b>PART NUMBER: LMA964MMA02040DB00</b>						
L	M	A	9	6	4	M M A 0 2 0 4 0 D B 0 0
KIT	E-SERIES	FRACTION OF E-SERIES	TYPE/SIZE	VERSION	TCR	TOLERANCE
LMA	96	4 = 1/4	MMA 0204	0 = Standard	D = ± 25 ppm/K	B = ± 0.1 %
<b>PRODUCT DESCRIPTION: LMA 96 4 MMA 0204-25 0.1 %</b>						
LMA	96	4	MMA 0204	-25	0.1 %	
KIT	E-SERIES	FRACTION OF E-SERIES	TYPE/SIZE	TCR	TOLERANCE	
LMA	96	4 = 1/4	MMA 0204	± 25 ppm/K	± 0.1 %	

### Note

- The product can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION