Data sheet

Potentiometer, compact, 22 mm, round, plastic, black, 10k ohm, with holder, screw terminal



| Product brand name | SIRIUS ACT |
|-------------------------------|--------------------|
| Product designation | Potentiometers |
| Design of the product | Compact unit |
| Product type designation | 3SU1 |
| Manufacturer's article number | |
| • of the supplied holder | 3SU1500-0AA10-0AA0 |

| Enclosure | |
|--------------------------|---|
| Number of command points | 1 |

| Actuator | |
|--|--|
| Design of the operating mechanism | Rotary knob |
| Manner of function of the actuating element | Infinitely variable adjustment, angle of rotation 280° |
| Color | |
| of the actuating element | black |
| Material of the actuating element | plastic |
| Shape of the actuating element | round |
| Outer diameter of the actuating element | 30 mm |
| Maximum deflection angle [°] | 280° |

| Product component front ring | No |
|---|---|
| | |
| Holder Material of the holder | Plastic |
| Material of the noider | Plastic |
| General technical data | |
| Insulation voltage | |
| • rated value | 500 V |
| Degree of pollution | 3 |
| Protection class IP | IP66, IP67, IP69(IP69K) |
| of the terminal | IP20 |
| Degree of protection NEMA rating | NEMA 1, 2, 3, 3R, 4, 4X, 12, 13 |
| Shock resistance | |
| ● acc. to IEC 60068-2-27 | Sinusoidal half-wave 50 g / 11 ms |
| • for railway applications acc. to DIN EN 61373 | Category 1, Class B |
| Mechanical service life (switching cycles) | |
| • typical | 25 000 |
| Reference code acc. to DIN EN 81346-2 | S |
| Reference code acc. to DIN EN 61346-2 | S |
| Connections/Terminals | |
| Type of electrical connection | screw-type terminals |
| Type of connectable conductor cross-sections | |
| solid with core end processing | 2x (0.5 0.75 mm²) |
| solid without core end processing | 2x (1.0 1.5 mm²) |
| finely stranded with core end processing | 2x (0.5 1.5 mm²) |
| finely stranded without core end processing | 2x (1,0 1,5 mm²) |
| at AWG conductors | 2x (18 14) |
| Tightening torque of the screws in the bracket | 1 1.2 N·m |
| Tightening torque | |
| with screw-type terminals | 0.8 1 N·m |
| Ambient conditions | |
| Ambient temperature | |
| during operation | -25 +70 °C |
| during storage | -40 +80 °C |
| Environmental category during operation acc. to IEC | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95 %, |
| 60721 | no condensation in operation permitted for all devices behind front |
| | panel) |
| Installation/ mounting/ dimensions | |
| Height | 40 mm |
| Width | 30 mm |
| Shape of the installation opening | round |
| Mounting diameter | 22.3 mm |
| Positive tolerance of installation diameter | 0.4 mm |

| Mounting height | 19.4 mm |
|--------------------|---------|
| Installation width | 30 mm |
| Installation depth | 46 mm |

Certificates/approvals

General Product Approval Declaration of Conformity Test Certificates









Miscellaneous

Special Test Certificate

| Test Certific- | other |
|----------------|-------|
| ates | |
| | |

Type Test Certificates/Test Report

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)


https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1200-2PS10-1AA0


Cax online generator


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SU1200-2PS10-1AA0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1200-2PS10-1AA0&lang=en







last modified: 02/21/2019