

Desktop Power Supply Unit



Features

- IEC/EN/UL 62368-1 & 60950-1
- 100-240 VAC Universal Input, Without Any Slide Switch
- Regulated Output With Low Ripple Noise
- Safety Agency Requirements and EMI/EMS Certified
- CEC, DoE Level VI, Energy Star, ErP Stage 2, CoC Tier 2, NRCan & GEMS Level VI
- No Load Power Consumption Less Than 0.21 W



Input Specification

Voltage	Universal 100 ... 240 VAC, Single Phase
Frequency	47 ... 63 Hz
Current	1.6 A max.
Inrush Current	80 A max. / 230 VAC Cold Start @ 25 °C, Full Load
Efficiency	88% @ 115 & 230 VAC
Power Consumption	210 mW @ 230 VAC & No Load
Power Factor	0.9 @ Full Load
Configuration	IEC60320 C14

Output Specification

Voltage	12 V \pm 5%
Current	9 A max.
Regulation	11.4 V min. / 12 V typ. / 12.6 V max.
Ripple & Noise	120 mV max.
Total Power	108 W max.
Load Regulation	\pm 5% (Typ.)
Transient Response	0.5 ms for 50% Load Change Typ.
Hold-Up Time	10 ms @ Full Load
Configuration	4-Pin Plug
DC Cord	14 AWG

Safety

Insulation Resistance	10 MOhm for 500 VDC
EMI Requirement	CE Class B, Conduction and Radiation Met
Approvals	CB / UL / cUL / FCC / GS / CE / PSE / BSMI / RCM / CCC
Over Voltage Protection (OVP)	V out * 150% (max.)
Short Circuit Protection (SCP)	Automatic recovery after short-circuit fault being removed
Over Current Protection (OCP)	I out * 170% (max.)
Grounding Test	Resistance 100 mOhm @ 25 A

Notes:

When short circuit protection or over current protection is activated, the power supply will shutdown automatically
Once the abnormal condition resulting in the failure is removed, the power supply will restart accordingly
When over voltage protection is activated, the power supply will shutdown

Electrical

Topology	Switching Flyback
Dielectric Withstand	3 kVAC Primary - Secondary for 1 min
Leakage Current	3.5 mA
Efficiency	DoE Level VI, Energy Star, ErP Stage 2, CoC Tier 2, NRCan & GEMS Level VI Certified
EMC Standards	EN55032 / EN61000-3-2,3 / EN55024
MTBF	300000 Calculated Hours at 25 °C

Desktop Power Supply Unit




Operation and Environment Performance


Operating Temperature	0 ... 40 °C
Storage Temperature	-20 ... 80 °C
Operating Humidity	20 ... 80% RH
Storage Humidity	10 ... 90% RH
Cooling	Natural Convection Cooling

Mechanical Specification

Cable Type	14 AWG, UL1185 Wire
Plug Type	4-Pin DIN
Cable Length	1 m
Case Dimensions (L*W*H)	168.1 x 65.9 x 39 mm
Material Flammability	UL94V-0
Weight	630 g, Typical




Cable & Plug Drawing




Desktop Power Supply Unit




Adapter Drawing




TOP-VIEW



BOTTOM-VIEW



SIDE-VIEW




FRONT-VIEW


Desktop Power Supply Unit



Derating Curve



Static Characteristics



Art Nr.
RND 320-00097