




MQS

TE Internal #: 5-968221-1

MQS, Automotive Terminals, Receptacle, Tab Width .63 mm [.025 in], Tab Thickness .025 in [.63 mm], Terminal Transmits 0 – 24 A (Low Power)

[View on TE.com >](#)

Terminals & Splices > Automotive Terminals > MQS, RECEPTACLE AND TAB



Terminal & Splice Type: **Receptacle**
 Mating Tab Width: **.63 mm [.025 in]**
 Mating Tab Thickness: **.63 mm [.025 in]**
 Terminal Transmits: **0 – 24 A (Low Power)**
 Wire Size: **.5 – .75 mm²**

[All MQS, RECEPTACLE AND TAB \(128\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body
Automotive Terminal Wire Type	Copper

Contact Features

Typical Current Rating	7.5 A
Crimp Type	F-Crimp
Terminal & Splice Type	Receptacle
Mating Tab Width	.63 mm [.025 in]
Mating Tab Thickness	.63 mm [.025 in]
Automotive Terminal Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)



Termination Features

Automotive Terminal Termination Method	Crimp
--	-------

Dimensions

Wire Size	.5 – .75 mm ²
Wire Size Search	.5 mm ² , .6 mm ² , .75 mm ²
Wire Insulation Diameter	1.3 – 1.9 mm [.051 – .074 in]

Usage Conditions

Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C [-40 – 248 °F]

Industry Standards

Agency/Standard	LV214
-----------------	-------

Packaging Features

Packaging Method	Reel
Packaging Quantity	10000

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-1579007-0
EXTRACTION TOOL



TE Part # 2305570-1
TERMINAL CUTTER, SIDE FEED



TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING



TE Part # 1-1579018-4
EXTRACTION TOOL



TE Part # 2209544-9
60P, PLUG ASSY, NORMAL CODING



TE Part # 2209545-1
94P, MQS CB, REC HSG, ASSY, SEALED



TE Part # 2-2151491-1
OCEAN_2.0_APPLICATOR-S-055F0800



TE Part # 2-2151491-2
OCEAN_2.0_APPLICATOR-S-055F0800



TE Part # 2-2836876-1
OCEAN_2.0_Applicator-S-055F0800



TE Part # 2-2836876-2
OCEAN_2.0_Applicator-S-055F0800



TE Part # 2151491-1
OCEAN_2.0_APPLICATOR-S-055F0800



TE Part # 2151491-2
OCEAN_2.0_APPLICATOR-S-055F0800



TE Part # 2209544-1
60P, MQS CB, REC HSG, ASSY, SEALED



TE Part # 2836876-1
OCEAN_2.0_Applicator-S-055F0800













TE Part # 2836876-2
OCEAN_2.0_Applicator-S-055F0800



TE Part # 5-2151491-1
OCEAN_2.0_APPLICATOR-S-055F0800



Also in the Series | MQS



Customers Also Bought





TE Part #1379100-2
COV+LEV MQS 18W 0DEG WHI



TE Part #1-1452424-3
BLIND PLUG FOR MCON 1.2 CB (0,75 MM?)



TE Part #1-1534093-1
MQS COVER 2X6 POS



TE Part #NB11716001
ATUM-8/2-0-35MM



TE Part #0989076013
RBK-ILS-125-NR2-0-27MM



TE Part #1534180-2
AMP MCP, UNSEALED CONNECTOR HOUSING

Documents

Product Drawings

MQS0,63 Sn rec CB unseal. 0,5-0,75

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-968221-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-968221-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-968221-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Micro Quadlok Interconnection System (MQS)

English

Product Specifications

Application Specification

German

Application Specification

English



Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English