




**Accessories for actuator/sensor cables  
male flange with strands, rear-mounted  
EC-FSFD5-0,5/16**



- M12 ♂ 1 male receptacle
- Protection class IP67
- Rear-mounted
- Connected via stranded wires

**Pin Assignment**



<b>Type designation</b>	EC-FSFD5-0,5/16
Ident no.	6934566
<b>Connector A side</b>	Male receptacle, M12 ♂ 1, Straight
Number of pins	4+PE
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, PA GF, Black
Flange housing	Brass, CuZn, nickel-plated
Screw-in thread seal	plastic, NBR
Screw-in thread	M16x1.5
Connection mode	Wire connection
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Protection class	IP67, (screwed together)
<b>Cable length</b>	0.5 m
Core insulation	PVC
Core colors	BN, WH, BU, BK, GNYE
Core cross-section	4x0.34mm <sup>2</sup>
Core cross-section	1x0.5mm <sup>2</sup>
<b>Electrical features at +20 °C</b>	
Rated voltage	60 V
Current	4 A
Insulation resistance	≥ 10 <sup>8</sup> Ω
Forward resistance	≤ 5 mΩ
<b>Mechanical and chemical properties</b>	
Ambient temperature	
Stationary	-30...+90°C