multicomp PRO








RoHS Compliant

Features

- · Small size and light weight
- · Reduction of assembly costs and matching with placement machines
- Reliability, high quality
- Suitable for IR reflow soldering

Construction




Applications


- Entertainment
- · Computer & Related Products
- Communication Equipment
- · Power Equipment
- · Measuring Instrument

	1	Alumina Substrate	4	Edge Electrode	7	Resistor Layer
	2	Bottom Electrode	5	Barrier Layer	8	Primary Overcoat
ĺ	3	Top Electrode	6	External Electrode	9	Secondary Overcoat

Dimensions








MCPNF42 / MCPNF43

Туре	Number of Resistors	L (mm)	W (mm)	H (mm)	A (mm)	A1 (mm)	B (mm)	C (mm)	Y (mm)	Weight (g) (1000pcs)
MCPNF22	2	1.2±0.1	1 ±0.1	0.35 ±0.1	0.43 ±0.1	-	0.82 ±0.05	0.22 ±0.1	0.3 ±0.15	1.6
MCPNF42	4	2 ±0.1	1 ±0.1	0.45 ±0.1	0.35 ±0.1	0.45 ±0.1	0.5 ±0.1	0.2 ±0.1	0.35±0.15	3.2
MCPNF43	4	3.2±0.1	1.55 ±0.1	0.55 ±0.1	0.45 ±0.15	0.6 ±0.1	0.8 ±0.05	0.2 ±0.1	0.47±0.15	10.2




multicomp PRO

Part Numbering



Derating Curve



E lectrical S pecifications

Item	Power Rating		Max.	Max.	Number	Resistan	ce Range	TOD	
Туре	at 70°C Jumper Rated Current	Operating Temp. Range	Operating Voltage	Overload Voltage	of Resistors	± 1% (E24, E96)	±5% (E24)	TCR (PPM/°C)	
	1/16 W					1Ω to 9.76Ω	1Ω to 9.1Ω	±500	
MCPNF22	lumpor:1A		25V	50V	2	10Ω to $1M\Omega$	10Ω to $1M\Omega$	±200	
	Jumper:1A					-	0Ω(<50mΩ	-	
MCPNF42	1/16 W	-55°C to +155°C				1Ω to $10M\Omega$	1Ω to $10M\Omega$	±200	
WICFINF42	Jumper:1A	00 0 10 1 100 0				-	0Ω(<50mΩ	-	
MCPNF43	1/10W 1/8W		50V	100V	4	1Ω to 10MΩ	1Ω to 10MΩ	±200	
	Jumper:1A					-	0Ω(<50mΩ	-	


Operating Voltage= $\sqrt{(P^*R)}$ or Max. operating voltage listed above, whichever is lower. Overload Voltage= $2.5 \sqrt{(P^*R)}$ or Max. overload voltage listed above, whichever is lower.






Equivalent Circuit Diagram





MCPNF42 / MCPNF43

Soldering Condition (IPC/JEDEC J-STD-020)



Environmental Characteristics

lta		Requirement		Took Mathead					
Item	±1%	±5%	Jumper	Test Method					
Temperature Coefficient of Resistance (T.C.R.)	As Spec.			JIS-C-5201-1 4.8 IEC-60115-1 4.8 At 25°C/-55°C and 25°C/+125°C, 25°C is the reference temperature					
Short Time Overload	± (1%+0.05Ω)	± (2%+0.05Ω)	<50mΩ	JIS-C-5201-1 4.13 IEC-60115-1 4.13 RCWV*2.5 or Max. Overload Voltage whichever is lower for 5 seconds					
Insulation Resistance	≥10G			JIS-C-5201-1 4.6 IEC-60115-1 4.6 Max. Overload Voltage for 1 minute					
Endurance	± (2%+0.1Ω)	± (3%+0.1Ω)	<50mΩ	JIS-C-5201-1 4.25 IEC-60115-1 4.25.1 70±2°C, RCWV for 1000 hrs with 1.5 hrs "ON" and 0.5 hr "OFF"					

Page <3>







Item		Requirement		Test Method				
item	±1%	±5%	rest method					
Damp Heat with Load	± (2%+0.1Ω)	± (3%+0.1Ω)	<50mΩ	JIS-C-5201-1 4.24 IEC-60115-1 4.24 40±2°C, 90~95% R.H., RCWV for 1000 hrs with 1.5 hrs "ON" and 0.5 hr "OFF"				
Dry Heat	± (1%+0.05Ω)	± (1.5%+0.1Ω)	<50mΩ	JIS-C-5201-1 4.23 IEC-60115-1 4.23.2 at +155°C for 1000 hrs				
Bending Strength	± (1%+0.05 Ω	± (1%+0.05 Ω	<50mΩ	JISC 5201 1 4.33 IEC60115 1 4.33 Bending once for60 seconds with 3mm				
Solderability	95% min. covera	ige		JISC 5201 1 4.17 IEC60115 1 4.17 245± 5°C for 3 seconds				
Resistance to Soldering Heat	± (0.5%+0.05 Ω	± (1%+0.05 Ω	<50mΩ	JISC 5201 1 4.18 IEC60115 1 4.18 260± 5°C for 10 seconds				
Voltage Proof	No breakdown o	r flashover		JISC 5201 1 4.7 IEC60115 1 4.7 1.42 times Max. Operat ing Voltage for 1 minute				
Leaching	Individual leachin Total leaching ar			JISC 5201 1 4.18 IEC 60068 2 58 8.2.1 260± 5°C for 30 seconds				
Rapid Change of Temperature	± (0.5%+0.05 Ω	± (1%+0.05 Ω	<50mΩ	JIS C 5201 1 4.19 IEC 60115 1 4.19 -55°C to +155°C, 5 cycles				

RCWV(Rated continuous working voltage)= $\sqrt{(P^*R)}$ or Max. Operating voltage whichever is lower Storage Temperature: 15°C to 28°C; Humidity < 80%RH Shelf Life: 2 years from production date.

R ecommend Land Pattern





MCPNF42 / MCPNF43




multicomp PRO

Туре	A (mm)	B (mm)	C (mm)	l (mm)	P (mm)
MCPNF22	1.5	1.25	-	0.35	0.8
MCPNF42	2.1	1.8	0.3	0.5	0.5
MCPNF43	3.1	2.85	0.45	0.8	0.8


Packaging

Reel Specifications & Packaging Quantity



Type	Paper	_	Tape Width	Reel Diameter	ΦA (mm)	ФВ (mm)	ΦC (mm)	W (mm)	T (mm)
MCPNF22	_	10k							
MCPNF42	Paper	TUK	8mm	7 inch	178.5 ±1.5	60+1/-0	13 ±0.2	9 ±0.5	12.5±0.5
MCPNF43]	5k							

Paper Tape Specifications



Туре	A (mm)	B (mm)	W (mm)	E (mm)	F (mm)	P₀ (mm)	P ₁ (mm)	P ₂ (mm)	ФD₀ (mm)	T (mm)
MCPNF22	1.2 ±0.1	1.45 ±0.1								0.43 ±0.1
MCPNF42	1.2 ±0.1	2.2 ±0.1	8 ±0.2	1.75 ±0.1	3.5 ±0.05	4 ±0.1	2 ±0.05	2 ±0.05	1.5 +0.1,-0	0.7 ±0.1
MCPNF43	1.95 ±0.1	3.5 ±0.1								0.85 ±0.1





Marking

No Marking for MCPNF22 Jumper for MCPNF42/MCPNF43: Letter "0"

1% for MCPNF42/MCPNF43: 4 digits marking (non-including E24 series)

Example

Resistance	102Ω	2.49ΚΩ	30K1Ω	49.9ΚΩ	121ΚΩ
marking	1020	2491	3012	4992	1213

1% & 5% for MCPNF42/MCPNF43: 3 digits marking in E24

Example: $101=100\Omega$ $102=1K\Omega$ (1st and 2nd are E24 code and 3rd code is multiplier)

TCOGE		E24 code	10	11	12	13	15	16	18	20	22	24	27	30	33	36	39	43	47	51	56	62	68	75	82	91
-------	--	-------------	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

