

Roller container with vice holder plate

With 5 fully extending drawers

Execution:

- Welded sheet steel structure with 4 rubber-tyred wheels, 2 of which are fixed wheels (diameter 300 mm) and 2 of which are guide rollers (diameter 200 mm), locking device
- With large folding steel tube push handle
- Top of deposit tray fitted with a ribbed rubber mat
- Tilt-proof due to built-in individual drawer pull-out lock
- Delivered without vice, please order separately (see no. 51028001 ATORN parallel vice, jaw width 100 mm)
- Vice can be attached to the upper frame of the trolley (carrier plate provided on frame)
- For suitable insert materials for drawers, see from no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

Art. no.	50282 197
Brand	HK
Manufacturer Part Number	50282197
Number of drawers	5 PCS
Pullout type	Full extension
Number of loading surfaces	1 PCS
Drawer front height	4 x 60 mm, 1 x 90 mm
Height	930/800 mm
Width	570 mm
Depth	680 mm
Drawer width (inner dimension)	450 mm
Drawer depth (inner dimension)	600 mm
Load-carrying capacity per drawer	70 kg
With single pull-out safety brake	Yes
Central locking	Yes
Lock type	DOM® locking system
With sliding handle	Yes
Load-carrying capacity	910 kg
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
Number of wheel adjusters	2 PCS
Material of wheel	Solid rubber
Wheel diameter	300/200 mm
Material	Sheet steel
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Gross Weight	89.000 kg
Product Group	501

EAN

4039247969616