



Finish : Reflector

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES 9245 876 49100 0833/000 p.190-1 Of 06/03/2012		HALOGEN LAMP INFRARED INDUSTRIAL REFLECTOR 14196Z/83 2500W 400V REFL					9245 876 49100 0833/000			21/09/2012					
REF. : PDM IRK 2012-011		DOCUMENTATION		UNIT mm	PROJ. EUROP 	2 SH	SH 190-1	10	1:1	A4					
NAME : J.P. CHARLIER		VALIDATION : A. PICHARD			DR. FISCHER Europe										
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															

PRODUCT REQUIREMENT SHEET

See LV 75-032

MEASURING VOLTAGE	400V (stabilisation 3 min.)
MEASURING POSITION	Horizontal
LIFE TEST POSITION	Horizontal
BURNING POSITION	P15
SWITCHING CYCLE	Continuous
AGEING	1h at rated voltage

	VALUE UNIT	TOLERANCE
WATTAGE	2500W	± 6 %
LIFE	5000 h	average
COLOR TEMPERATURE	Clear lamp Lamp with reflector	2700 K NA ± 100 K
FLUX (HeLeN lamp)	Clear lamp Reduction	NA NA
IRRADIANCE LEVEL	21500W / m ²	Mini
WEIGHT	48 g	

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES :		HALOGEN LAMP						9245 876 49100			06/03/2012				
9245 876 49100		INFRARED INDUSTRIAL REFLECTOR						0833/000							
0833/000 p. 190-2		14196Z/83 2500W 400V REFL													
Of 18/10/2011		REF. : PDM IRK 2012-007		DOCUMENTATION	UNIT mm	PROJ EUROP	2	SH	SH	190-2	10		A4		
NOM : J.P. CHARLIER		VALIDATION : A. PICHARD						DR. FISCHER Europe							
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															