



Product Information

Product Category	FLOORCARE
Unit Barcode	5016368092088
Outer Carton Barcode	
Commodity Code	8508110000
Country of Origin	CHINA
Primary Colour	SILVER
Finish	PLASTIC
Primary Material	PLASTIC
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	

General Product Specification

Voltage	230
Frequency	50
Wattage	300
Rated Current	2.9
Fuse Rating	13
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	5
Class	CLASS II
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	1118	132	244
Packaged Dimensions H x W x D (mm)	685	145	140
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			1.94
Unit Packaged Weight (Kg)			2.35
Carton Weight (Kg)			
EPS (Kg)		PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.02	Card / Paper (Kg)	0.39
Aluminium (Kg)		Steel (Kg)	

Category Specific Technical Information

Corded or Cordless	CORDED	Battery Charge Time	
Wet & Dry:	NO	Bagged/Bag	BAGLESS
Tube Material	METAL	Battery Type	
Suitable Floor Types	CARPET & HARD FLOOR	Battery EN Number	
Cyclonic System		Battery Level Indicator	
Filter Type	HEPA	Battery Milli-Ampere-Hours	
Dust Capacity	0.7	Battery Voltage	
Dirty Water Capacity		Battery Watt-Hours	
Clean Water Capacity		Battery Weight	
Motor Type	AC	Air Flow Rate	
Motor Max Capacity	330	Cleaning Path Width	
Maximum Suction Power	60	Handheld Vacuum Nozzle Width	
Maximum Vacuum Suction	10	Cleaning Range	
Number of Speed Settings	1	Hose Length	
Run Time	High: Low:	LED Lights	
Allergy/Asthma Approval	NO	Motorised Floorhead	
Lithium Battery Energy Capacity		Noise Level	80
Number of Lithium Ion Cells		Number of Accessories Included	1
		Adjustable Floorhead	NO