

Trade name: SA47, SA47-HT, SA47-LA

Current version: 1.0.0, issued: 05.10.2022 Replaced version: -, issued: - Region: GB

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name

SA47, SA47-HT, SA47-LA

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture

Heat shrink tube

Electrical insulation

Uses advised against

No data available.

1.3 Details of the supplier of the safety data sheet

Address

Hellermann Tyton GmbH Großer Moorweg 45 25436 Tornesch

Telephone no. +49 4122 701-1

e-mail substance.legalcompliance@hellermanntyton.de

Advice on Safety Data Sheet

sdb_info@umco.de

1.4 Emergency telephone number

For medical advice (in German and English): +49 (0)551 192 40 (Giftinformationszentrum Nord)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification information

This product is an article in the sense of Article 3 of Regulation (EC) 1907/2006 (REACH) and is not subject to labelling according to Article 1, Regulation (EC) 1272/2008 (CLP).

Provision of a safety data sheet is not mandatory for articles according to Article 31 of Regulation (EC) 1907/2006 (REACH) and is done on a voluntary basis.

2.2 Label elements

Not relevant

2.3 Other hazards

No data available.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable. The product is not a substance.

3.2 Mixtures

Hazardous ingredients

This product does not contain substances to be mentioned according to EU Regulation No 1907/2006 (REACH), annex II.

3.3 Other information

Plastic tube

SECTION 4: First aid measures

4.1 Description of first aid measures

General information



Trade name: SA47, SA47-HT, SA47-LA

Current version: 1.0.0, issued: 05.10.2022 Replaced version: -, issued: - Region: GB

Remove contaminated clothing and shoes and launder thoroughly before reusing. In case of persisting adverse effects, consult a physician.

After inhalation

Not relevant due to the compact form of the product. When vapours are intensively inhaled, seek medical help immediately.

After skin contact

After contact with molten product, cool quickly with cold water.

After eye contact

Remove contact lenses. Rinse eye thoroughly under running water keeping eyelids wide open and protecting the unaffected eye (at least 10 to 15 minutes).

After ingestion

Ingestion is not considered a possible route of exposure.

4.2 Most important symptoms and effects, both acute and delayed

No data available.

4.3 Indication of any immediate medical attention and special treatment needed

No data available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

carbon dioxide; foam; extinguishing powder; water spray jet; water mist

Unsuitable extinguishing media

High power water jet

5.2 Special hazards arising from the substance or mixture

In the event of fire, the following can be released: Carbon dioxide (CO2); Carbon monoxide (CO)

5.3 Advice for firefighters

Use self-contained breathing apparatus. Wear protective clothing.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Refer to protective measures listed in sections 7 and 8.

For emergency responders

Personal protective equipment (PPE) - see section 8.

6.2 Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

6.3 Methods and material for containment and cleaning up

Collect mechanically. When collected, handle material as described under the section heading "Disposal considerations".

6.4 Reference to other sections

Information regarding safe handling, see section 7. Information regarding personal protective measures, see section 8. Information regarding waste disposal, see section 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling

Recommended max. operating temperature is 130 °C. Do not heat over 300 °C to avoid harmful vapors which may be formed at high temperatures.

General protective and hygiene measures



Trade name: SA47, SA47-HT, SA47-LA

Current version: 1.0.0, issued: 05.10.2022 Replaced version: -, issued: - Region: GB

Do not eat, drink or smoke during work time. Keep away from foodstuffs and beverages. Wash hands before breaks and after work. Do not inhale dust.

7.2 Conditions for safe storage, including any incompatibilities

Technical measures and storage conditions

Keep container tightly closed and dry in a cool, well-ventilated place. Protect from heat and direct sunlight.

Requirements for storage rooms and vessels

Containers which are opened must be carefully resealed and kept upright to prevent leakage. Always keep in containers of same material as the original.

Incompatible products

Substances to be avoided, see section 10.

7.3 Specific end use(s)

No data available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

No parameters available for monitoring.

8.2 Exposure controls

Appropriate engineering controls

Ensure adequate ventilation, local exhaust at the work station if necessary.

Personal protective equipment

Respiratory protection

If workplace exposure limits are exceeded, a respiration protection approved for this particular job must be worn. In case of dust formation, take appropriate measures for breathing protection in the event that workplace threshold values are not specified.

Eye / face protection

Safety glasses (EN 166)

Hand protection

Use protective gloves when handling hot product. Before use, the protective gloves should be tested in any case for its specific work-station suitability (i.e. mechanical resistance, product compatibility and antistatic properties). Adhere to the manufacturer's instructions and information relating to the use, storage, care and replacement of protective gloves. Protective gloves shall be replaced immediately when physically damaged or worn. Design operations thus to avoid permanent use of protective gloves.

Other

Chemical-resistant work clothes.

Environmental exposure controls

No data available.

Boiling point / boiling range

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

State of aggregation
solid
Form
ubes
Colour
olack
Odour
light polymer-/latex-odor
OH value
No data available



Trade name: SA47, SA47-HT, SA47-LA

Current version: 1.0.0, issued: 05.10.2022 Replaced version: -, issued: -Region: GB

No data available	

Melting point/freezing point	
Value	120 - 130 °C
Comments	The material has melting point but outer jacket will not flow over the

Decomposition temperature

No data available

Flash point No data available

Ignition temperature

No data available

Flammability

No data available

Lower explosion limit

No data available

Upper explosion limit

No data available

Vapour pressure

No data available

Relative vapour density

No data available

Relative density

No data available

Density

No data available

Solubility

No data available

Partition coefficient n-octanol/water (log value)

No data available

Kinematic viscosity

No data available

Particle characteristics

No data available

Other information

Other information

No data available.

SECTION 10: Stability and reactivity

10.1 Reactivity

No data available.

10.2 Chemical stability

Stable under recommended storage and handling conditions (See section 7).

Possibility of hazardous reactions

Dangerous reactions are not to be expected when handling product according to its intended use.

10.4 Conditions to avoid

High temperatures.

10.5 Incompatible materials

None, if handled according to order.



Trade name: SA47, SA47-HT, SA47-LA

Current version: 1.0.0, issued: 05.10.2022 Replaced version: -, issued: - Region: GB

10.6 Hazardous decomposition products

Carbon monoxide; Halogen hydrocarbons

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity

No data available

Acute dermal toxicity
No data available

Acute inhalational toxicity

No data available

Skin corrosion/irritation

No data available

Serious eye damage/irritation

No data available

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Reproduction toxicity

No data available

Carcinogenicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration hazard

No data available

11.2 Information on other hazards

Endocrine disrupting properties

No data available.

Other information

No data available.

SECTION 12: Ecological information

12.1 Toxicity

Toxicity to fish (acute)

No data available

Toxicity to fish (chronic)

No data available

Toxicity to Daphnia (acute)

No data available

Toxicity to Daphnia (chronic)

No data available

Toxicity to algae (acute)

No data available



Trade name: SA47, SA47-HT, SA47-LA

Current version: 1.0.0, issued: 05.10.2022 Replaced version: -, issued: - Region: GB

Toxicity to algae (chronic)

No data available

Bacteria toxicity

No data available

12.2 Persistence and degradability

No data available.

12.3 Bioaccumulative potential

No data available.

12.4 Mobility in soil

No data available.

12.5 Results of PBT and vPvB assessment

No data available.

12.6 Endocrine disrupting properties

No data available.

12.7 Other adverse effects

No data available.

12.8 Other information

Other information

Do not discharge product unmonitored into the environment.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product

Disposal of the product should be carried out in accordance with all applicable regulations following consultation with the responsible local authority and the disposal company in an authorised and suitable disposal facility.

Allocation of a waste code number, according to the European Waste Catalogue, should be carried out in agreement with the regional waste disposal company.

Packaging

Residues must be removed from packaging and when emptied completely disposed of in accordance with the regulations for waste removal. Incompletely emptied packaging must be disposed of in the form of disposal specified by the regional disposer.

SECTION 14: Transport information

14.1 Transport ADR/RID/ADN

The product is not subject to ADR/RID/ADN regulations.

14.2 Transport IMDG

The product is not subject to IMDG regulations.

14.3 Transport ICAO-TI / IATA

The product is not subject to ICAO-TI / IATA regulations.

14.4 Other information

No data available.

14.5 Environmental hazards

Information on environmental hazards, if relevant, please see 14.1 - 14.3.

14.6 Special precautions for user

No data available.

14.7 Maritime transport in bulk according to IMO instruments

Not relevant

SECTION 15: Regulatory information



Trade name: SA47, SA47-HT, SA47-LA

Current version: 1.0.0, issued: 05.10.2022 Replaced version: -, issued: - Region: GB

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture EU regulations

Regulation (EC) No 1907/2006 (REACH) Annex XIV (List of substances subject to authorisation)

According to the data available and/or specifications supplied by upstream suppliers, this product does not contain any substances considered as substances requiring authorisation as listed on Annex XIV of the REACH regulation (EC) 1907/2006.

REACH candidate list of substances of very high concern (SVHC) for authorisation

The article contains following substance/s that is/are considered substances meeting the criteria for inclusion in annex XIV (List of Substances Subject to Authorisation) as laid down in Article 57 and article 59 of REACH (EC) 1907/2006.

No	Substance name	CAS no.	EC no.
1	6,6'-DI-TERT-2,2'-METHYLENEDI-P-KRESOL (BPH)	119-47-1	204-327-1

Regulation (EC) No 1907/2006 (REACH) Annex XVII: RESTRICTIONS ON THE MANUFACTURE, PLACING ON THE MARKET AND USE OF CERTAIN DANGEROUS SUBSTANCES, MIXTURES AND ARTICLES

The product contains following substance(s) that are considered being subject to REACH regulation (EC) 1907/2006 annex XVII.

I	No	Substance name		CAS no.	EC no.	No	
•	1	6,6'-DI-TERT-2,2'-METHYLENEDI-P-KRESOL (B	BPH)	119-47-1	204-327-1	30, 75	

Directive 2012/18/EU on the control of major-accident hazards involving dangerous substances

This product is not subject to Part 1 or 2 of Annex I.

Other regulations

Adhere to the national sanitary and occupational safety regulations when using this product.

15.2 Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

Sources of key data used to compile the data sheet:

Regulation (EC) No 1907/2006 (REACH), 1272/2008 (CLP) as amended in each case.

Directives 2000/39/EC, 2006/15/EC, 2009/161/EU, (EU) 2017/164.

National Threshold Limit Values of the corresponding countries as amended in each case.

Transport regulations according to ADR, RID, IMDG, IATA as amended in each case.

The data sources used to determine physical, toxic and ecotoxic data, are indicated directly in the corresponding section.

Creation of the safety data sheet

UMCO GmbH - D-21107 Hamburg, Georg-Wilhelm-Strasse 187, Tel.: +49(40)555 546 300, Fax: +49(40)555 546 357, e-mail: umco@umco.de

This information is based on our present knowledge and experience.

The safety data sheet describes products with a view to safety requirements.

It does not however, constitute a guarantee for any specific product properties and shall not establish a legally valid contractual relationship.

Document protected by copyright. Alterations or reproductions require the express written permission of UMCO GmbH

Prod-ID 789576