



Model Number

LLR 04-1,6-0,5-QW 1X4

Glass fiber optic - diffuse with metal silicone covering

Features

- Chemical-resistant
- Optical face across the direction of fiber

Series

Fiber optic amplifiers

Device series MLV41-LL

Description

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



Technical data

General specifications

Fiber optic length	l	500 mm
Fiber optic diameter	d	7.3 mm
Adapter form		04
End piece		Thread / cylindrical right angle
Bending radius		min. 25 mm
Fiber bundle diameter		1 x 2.15 mm / optical face: 1 x 3.6 mm ²
Fiber configuration	Fv	optical separated
Angle of divergence		approx. 69 °

Ambient conditions

Ambient temperature		-20 ... 85 °C (-4 ... 185 °F) [Adapter]
		-40 ... 180 °C (-40 ... 356 °F) [End head and Covering]
Storage temperature		-20 ... 85 °C (-4 ... 185 °F)

Mechanical specifications

Protection degree		IP65
Material		
Optical face		glass
Sheathing		Metal-silicon
Core		Glass fiber
End piece		Stainless steel 1.4305 / AISI 303
Adapter		PVC
Extraction force		at probe at 20°C: 120 N

Dimensions

