


SPECIFICATION

Part No. : **GA.110.101111**

Product Name : 4G/3G/2G High Gain Magnetic Mount Ultra-Wideband Antenna

Feature : LTE / GSM / CDMA /DCS /PCS / WCDMA / UMTS / HSDPA / GPRS / EDGE / GPS / Wi-Fi 698MHz to 960MHz, 1575.42MHz, 1710MHz to 2700MHz, 3500MHz 1m RG174 Cable, SMA(M) Connector Typical 40% Efficiency and 3dBi Peak Gain Robust High Strength Super Magnet Mount Custom cables and connectors available RoHS Compliant





1. Introduction

The GA.110 magnetic ultra-wideband cellular antenna delivers stable high omnidirectional gain and efficiencies across all common 4G, 3G and 2G global cellular bands from 700 MHz to 3.5 GHz.

This high performing antenna can be used for all cellular devices and will not require changing antennas when deploying from country to country or technology to technology like CDMA to GSM or 4G to 3G. Being magnetic mount it is designed to be mounted on a ground plane for optimal performance. A reliable return loss of <10dB when mounted on a metal plate ensures it complies with the industry standards set by module makers and networks worldwide. Taoglas recommends using the antenna with 1m cable length or less and can provide customized connectors and cable lengths upon customer requirements.

The strong magnet base is extremely stable and robust, using only high quality neodymium magnets for a secure magnetic mount to ensure a high pull force to disengage.



2. Specification

ELECTRICAL								
Frequency (MHz)	698~800	824~960	1575.42	1710~1880	1850~1990	1710~2170	2400~2700	3500
Peak Gain (dBi)								
30x30cm GP (1m RG174)	1.8	2.6	1.3	2.5	2.3	3.9	2.9	0.6
30x30cm GP (2m RG174)	-1.0	0.9	0.9	3.9	2.8	2.5	2.2	-0.6
30x30cm GP (3m RG174)	-2.5	-0.1	-1.3	1.2	0.1	1.2	-0.5	-1.6
Average Gain (dBi)								
30x30cm GP (1m RG174)	-4.9	-2.4	-3.4	-2.7	-3.8	-3.3	-4.4	-7.2
30x30cm GP (2m RG174)	-6.3	-3.1	-4.4	-3.9	-4.3	-4.1	-5.4	-5.5
30x30cm GP (3m RG174)	-7.2	-4.4	-6.2	-5.5	-6.3	-6.1	-7.4	-8.9
Efficiency (%)								
30x30cm GP (1m RG174)	33.6	57.1	46.2	55.0	41.8	47.8	36.9	19.0
30x30cm GP (2m RG174)	23.9	48.7	36.5	41.3	37.3	39.5	29.0	28.0
30x30cm GP (3m RG174)	19.7	36.2	24.0	28.5	21.8	25.0	19.0	13.0
Impedance	50Ω							
Polarization	Linear							
Radiation Pattern		Omni						
Input Power	50 W							



MECHANICAL						
Base Diameter	50mm					
Whip Diameter	298mm					
Whip Material	Coated Brass					
Connector	SMA Male					
ENVIRONMENTAL						
Temperature Range	-40°C to 85°C					
Humidity	Non-condensing 65°C 95% RH					




LTE BANDS							
Band Number	LTE / LTE-Advanced	/ TD-SCDMA					
	Uplink	Downlink	Covered				
1	UL: 1920 to 1980	DL: 2110 to 2170	\checkmark				
2	UL: 1850 to 1910	DL: 1930 to 1990	\checkmark				
3	UL: 1710 to 1785	DL: 1805 to 1880	\checkmark				
4	UL: 1710 to 1755	DL: 2110 to 2155	\checkmark				
5	UL: 824 to 849	DL: 869 to 894	\checkmark				
7	UL: 2500 to 2570	DL:2620 to 2690	\checkmark				
8	UL: 880 to 915	DL: 925 to 960	\checkmark				
9	UL: 1749.9 to 1784.9	DL: 1844.9 to 1879.9	✓				
11	UL: 1427.9 to 1447.9	DL: 1475.9 to 1495.9	×				
12	UL: 699 to 716	DL: 729 to 746	\checkmark				
13	UL: 777 to 787	DL: 746 to 756	\checkmark				
14	UL: 788 to 798	DL: 758 to 768	\checkmark				
17	UL: 704 to 716	DL: 734 to 746 (LTE only)	\checkmark				
18	UL: 815 to 830	DL: 860 to 875 (LET only)	\checkmark				
19	UL: 830 to 845	DL: 875 to 890	\checkmark				
20	UL: 832 to 862	DL: 791 to 821	\checkmark				
21	UL: 1447.9 to 1462.9	DL: 1495.9 to 1510.9	×				
22	UL: 3410 to 3490	DL: 3510 to 3590	×				
23	UL:2000 to 2020	DL: 2180 to 2200 (LTE only)	\checkmark				
24	UL:1625.5 to 1660.5	DL: 1525 to 1559 (LTE only)	\checkmark				
25	UL: 1850 to 1915	DL: 1930 to 1995	\checkmark				
26	UL: 814 to 849	DL: 859 to 894	\checkmark				
27	UL: 807 to 824	DL: 852 to 869 (LTE only)	\checkmark				
28	UL: 703 to 748	DL: 758 to 803 (LTE only)	\checkmark				
29	UL: -	DL: 717 to 728 (LTE only)	\checkmark				
30	UL: 2305 to 2315	DL: 2350 to 2360 (LTE only)	\checkmark				
31	UL: 452.5 to 457.5	DL: 462.5 to 467.5 (LTE only)	×				
32	UL: -	DL: 1452 - 1496	×				
35	1850 t	\checkmark					
38	2570 t	\checkmark					
39	1880 t	\checkmark					
40	2300 t	✓					
41	2496 t	\checkmark					
42	3400 to 3600 ×						
43	3600 t	×					

*Covered bands represent an efficiency greater than 20%




3. Antenna Characteristics




3.1. Return Loss










3.3. Average Gain








4. Antenna Radiation Patterns

4.1. Antenna setup (On 300x300mm ground plane with 1m


RG174 cable)








4.2. Radiation Patterns

XY Plane














XZ Plane











5. Mechanical Drawing





6. Packaging





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.