

118-05050

Article Number: 118-05050

Outside Serrated Cable Ties, 50lb. 8" Max. Bun. Dia 1.95" PA66HS, Black, 100/pk



Download spec sheet

Base Data

Local Order Number 118-05050
Type T50ROS
Color Black (BK)

Features and Benefits

- Outside serrations minimize damage to cables, while still providing high tensile strength and low insertion force.
- Contour style head design provides additional space in constrained areas.
- Heat stabilized material provides excellent resistance to high heat exposures.

Product Description HellermannTyton outside serrated cable ties are designed with a smooth inside surface to help minimize indentation or damage to wire and cable insulation, while offering high tensile strength and low insertion force. The contour style head takes up less space than traditional style cable ties making it ideal for space constrained areas. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Outside Serrated Cable Ties, 50lb. 8" Max. Bun. Dia 1.95" PA66HS, Black, 100/pk

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225 N

Length L (Imperial) 8.0 "

Length L (Metric) 200 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.18 "

Width W (Metric) 4.6 mm

Height H (Imperial) 0.051 "

Height H (Metric) 1.3 mm

Bundle Diameter Min. (Imperial) 0.063 "

Bundle Diameter Min. (Metric) 1.6 mm

Bundle Diameter Max. (Imperial) 1.95 "

Bundle Diameter Max. (Metric) 50.0 mm

Thickness T (Imperial) 0.05 "

Cable Tie Head Length (Imperial) 0.26 "

Cable Tie Head Width (Imperial) 0.31 "

Thickness T (Metric) 1.3 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100 Pieces
Carton Quantity	7000 Pieces
Weight (Metric)	1.3 kg

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Certification/Specification	PAN6481