

## Electronic 3-point internal micrometer

Digital ABS Borematic

Mitutoyo

### Application:

For measuring through-bores and short centring shoulders in series production.

### Execution:

- LCD display, 11 mm high
- Titanium coated
- GO/NG tolerance judgement function
- Preset function
- ON/OFF
- Digimatic
- ABS function
- HOLD function
- Tolerance display
- Locking function

### Advantage:

- Quick and easy measurement. Suitable for series measurements
- 330° rotating display unit allows easy reading at any working angle

### Delivery:

Includes box, key, battery, factory test certificate



<b>Art. no.</b>	<b>32017 760</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	568-464
<b>Min./max. length measuring range in inches</b>	0.5-0.65 in
<b>Data transmission type</b>	DIGIMATIC
<b>Digit increment</b>	0.00005 in
<b>Design</b>	Metric, Imperial
<b>Error limit</b>	0.00025 in
<b>Digit height</b>	11 mm
<b>Display</b>	Digital
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	1,5 V SR44
<b>Calibration Group</b>	I
<b>Gross Weight</b>	1.825 kg
<b>Product Group</b>	3MA

### EAN

4946368636498