

## Heavy-duty cabinet with central partition

With solid sheet metal doors, with drawers and shelves

**RasterPlan**

### Application:

For a total loading capacity of up to 1.65 t for very heavy loads, particularly suitable for storage of the heaviest tools, such as embossing and punching dies.

### Execution:

- Extremely stable welded steel structure with brazed corners, with central partition
- Smooth fronts due to flush overlay doors, opening angle more than 200°, continuous rod guiding
- Doors can be locked simultaneously with a triple-point security cylinder lock, incl. 2 keys
- Cabinet base can carry a load of up to 400 kg

### Delivery:

Additional door designs (for 1950 mm height), e.g. perforated or slotted panel doors and sidewall lining, drawer locks and suitable insert materials with compartment dividers, additional group keys or main keys and further paint colours deliverable on request.



<b>Art. no.</b>	<b>50147 231</b>
<b>Brand</b>	RASTERPLAN
<b>Manufacturer Part Number</b>	1472.01.2024
<b>Door design</b>	Full-sheet panel
<b>Width</b>	1000 mm
<b>Depth</b>	600 mm
<b>Height</b>	1110 mm
<b>Number of shelves</b>	2 PCS
<b>Shelf width</b>	1000 mm
<b>Shelf depth</b>	600 mm
<b>Load-carrying capacity per shelf</b>	80 kg
<b>Number of drawers</b>	6 PCS
<b>Drawer front height</b>	2 x 100 mm, 2 x 125 mm, 2 x 175 mm
<b>Drawer width (inner dimension)</b>	889 mm
<b>Drawer depth (inner dimension)</b>	483 mm
<b>Load-carrying capacity per drawer</b>	110 kg
<b>Pullout type</b>	Full extension
<b>With partition wall</b>	Yes
<b>Load-carrying capacity</b>	1650 kg
<b>Central locking</b>	Yes
<b>Lock type</b>	Twist-grip lock with three-point fastening
<b>Material</b>	Sheet steel
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Surface</b>	Powder-coated
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Gross Weight</b>	118.000 kg
<b>Product Group</b>	5AC

### EAN

4251142240069