

Angular milling cutter 90°

For indexable milling inserts LN.X 1006..

ATORN®

Application


4 flutes per indexable milling insert and special chip shape geometry for profitability and high cutting rates when milling faces, milling corners, trimming and milling grooves.

Version

- Wear-resistant, nickel-plated version
- With internal cooling

Advantage

- 4 cutting edges on one double-sided indexable insert
- Special chip shape geometry for low power consumption
- Thick inserts



Art. No.	16016 363
Cutting edge diameter	63 mm
Length	40 mm
Bore diameter	22 mm
max. ap	9 mm
Number of cutting edges	9 PCS
Suitable indexable insert no.	1

EAN-Code

4050293344493