

SC torus milling cutter

4 cutters, ULTRA-coated

ATORN[®]



Application

Shank or torus milling cutter for universal machining.

Version

- Solid carbide ultra-fine grain
- Straight shank in accordance with DIN 6535 HA
- Centre cutting
- ULTRA-coated
- Edge protection chamfer/edge radius
- Extra-long design with no clearance

Art. no.	16862 082
Cutting material	VHM
Surface	ULTRA
Type	N
Number of cutting edges	4 PCS
Twist angle	52°
Tool holding device	HA parallel shank
Overall length	Normal
Cutting edge diameter	8 mm
Cutting edge length	19 mm
Clearance length	25 mm
Length	63 mm
Clearance diameter	7.7 mm
Shaft diameter	8 mm
Edge radius	1 mm
fz steel 1300	0.05 mm

EAN-Code

4050293092936