

Mobile collection tray

With perforated panel

Application:

mobile, secure and easy filling of oils etc. at various points of consumption from 60-l and 200-l drums.

Execution:

- 3-mm thick welded sheet steel structure
- Stable, zinc-plated sheet steel panel with square perforation (10x10 mm), 38 mm hole intervals, for free positioning of tool holders
- hot-dip galvanised sliding handles
- with galvanised grating (carrying capacity 1000 kg/m²)
- 2 steering rollers and 2 fixed castors



Art. no.	50060 529
Collection volume	60 l
Max. number of 60-litre containers	2
Length	570 mm
Width	890 mm
Height	1685 mm
For liquids hazardous to water GHS 1-4	Yes
For flammable liquids GHS 1-3	Yes
Declaration of conformity in acc. with StawaR	Yes
With grating	Yes
Material	Sheet steel
Surface	Zinc plated
Colour	Silver coloured
Gross Weight	68.000 kg
Product Group	5AI

EAN

4052462060913