



### Product Information

|                      |               |
|----------------------|---------------|
| Product Category     | DEHUMIDIFIERS |
| Unit Barcode         | 5016368065426 |
| Outer Carton Barcode |               |
| Commodity Code       | 8415830090    |
| Country of Origin    | CHINA         |
| Primary Colour       | WHITE         |
| Finish               | PLASTIC       |
| Primary Material     | PLASTIC       |
| Warranty             | 2             |
| Self Assembly        | NO            |
| Perishable Item      | NO            |
| Hazardous Item       | NO            |

### General Product Specification

|                     |         |
|---------------------|---------|
| Voltage             | 230     |
| Frequency           | 50      |
| Wattage             | 250     |
| Rated Current       | 1.26    |
| Fuse Rating         | 10      |
| Plug Type           | BS 1363 |
| Cable Diameter      | 0.75    |
| Cable Length        | 1.8     |
| Class               | CLASS I |
| Conformity Markings | CE+UKCA |

### Packaging & Shipping Information

|  |       |                         |      |
|--|-------|-------------------------|------|
| Product Dimensions H x W x D (mm)      | 460   | 280                     | 240  |
| Packaged Dimensions H x W x D (mm)     | 528   | 315                     | 284  |
| Outer Carton Dimensions H x W x D (mm) |       |                         |      |
| Outer Carton Qty.                      |       |                         |      |
| Unit Weight (Kg)                       |       |                         | 10   |
| Unit Packaged Weight (Kg)              |       |                         | 10   |
| Carton Weight (Kg)                     |       |                         |      |
| EPS (Kg)                               | 0.147 | PPT Exempt Plastic (Kg) |      |
| Other Plastic (Kg)                     |       | Card / Paper (Kg)       | 1007 |
| Aluminium (Kg)                         |       | Steel (Kg)              |      |

### Category Specific Technical Information

|                                     |                      |   |       |
|-------------------------------------|----------------------|---|-------|
| Adjustable Louvres                  | NO                   | Maximum Air Flow                              | 120   |
| Annual Energy Consumption           |                      | Maximum Delay Time                            | 24    |
| Auto Defrost                        | YES                  | Maximum Room Size                             | 20    |
| Auto Restart                        | YES                  | Number of Fan Speeds                          | 2     |
| Auto Shutoff                        | YES                  | Operating Temperature Range                   | ##### |
| Carry Handle                        | YES                  | Overheat Protection                           | YES   |
| Castors                             | YES                  | Power Consumption at Rate at 27oC and 60oC RH | 210   |
| Child Lock                          | YES                  | Power Consumption at Rate at 30oC and 80oC RH | 250   |
| Continuous Drainage Hose Length     | 0.3                  | Refrigerant Type                              | R290  |
| Continuous Drainage Option          | YES                  | Refrigerant Weight                            | 45    |
| Dehumidifier Type                   | COMPRESSOR           | Remote Control                                | NO    |
| Delay Off Timer                     | YES                  | Thermostatic Cut Off                          | YES   |
| Digital Display                     | YES                  | Tip Over Switch                               | NO    |
| Extraction Rate at 27oC and 60oC RH | 6                    | Variable Humidistat                           | YES   |
| Extraction Rate at 30oC and 80oC RH | 12                   | Water Level Indication Window                 | NO    |
| Filter Type                         | ACTIVE CARBON FILTER | Water Tank Full Indicator                     | YES   |
| Laundry Mode                        | YES                  | Water Tank Size                               | 2.2   |