Features

Regulated Converter

- Universal input 85-264VAC
- <250mW No load power consumption
- Class II installations (without FG)
- -25°C to +80°C Operating temperature, with derating
- Continuous SCP, OCP
- IEC/EN60950 & IEC/EN/UL62368 certified

Description

The RAC01-GB series are low cost AC/DC power supplies, ideal for PCB mounted, compact, board level industrial applications. They feature universal AC input voltage range, regulated and short-circuit-proof isolated DC outputs, low standby power consumption and -25°C to +80°C operating temperature range. The RAC01-GB have a built-in Class B / FCC Part 15 EMC filter, are certified to EN60950 and EN62368 safety standards and come with a three year warranty.



RAC01-GB

1 Watt
Single
Output
EMC Class B















Selection Guide

Part Number	Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ [%]	Max. Capacitive Load ⁽¹⁾ [μF]
RAC01-3.3SGB	85-264	3.3	303	63	500
RAC01-05SGB	85-264	5	200	63	500
RAC01-12SGB	85-264	12	83	68	200
RAC01-24SGB	85-264	24	42	63	200

Notes:

Note1: Measured with all input voltages at +25°C with constant resistant mode at full load

Model Numbering



Ordering Examples:

RAC01-12SGB 12Vout Single Output EMC Class B



Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)


BASIC CHARACTERISTICS						
Parameter	Cor	Condition			Тур.	Max.
Internal Input Filter				Pi-type		
Input Voltage Range (2,3,4)	nom. Vir	n = 230VAC		85VAC	230VAC	264VAC
Input Current		115VAC 230VAC			25mA 18mA	30mA 20mA
Inrush Current	cold start at +25°C	cold start at +25°C 115VAC 230VAC				30A 40A
No load Power Consumption					180mW	250mW
Input Frequency Range				47Hz		63Hz
Minimum Load						
Power Factor		115VAC 230VAC			0.5 0.38	
Start-up Time		115VAC 230VAC			250ms 200ms	2s 2s
Hold-up time		115VAC 230VAC				20ms 80ms
Internal Operating Frequency	100% load	at nominal Vin			65kHz	
		0°C to 80°C	3.3Vout 5Vout 12Vout 24Vout			100mVp-p 100mVp-p 200mVp-p 240mVp-p
Output Ripple and Noise	20MHz BW	-25 °C to 0°C	3.3Vout 5Vout 12Vout 24Vout			200mVp-p 200mVp-p 300mVp-p 300mVp-p


Notes:

Note2: No proper operation with DC input voltage

Note4: Refer to "Line Derating"

Efficiency vs. Load









Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)

REGULATIONS		
Parameter	Condition	Value
Output Accuracy	-25°C to +80°C	±6.0% max.
Line Regulation	-25°C to +80°C	±2.0% max.
Load Regulation	-25°C to +80°C	6.0% max.





PROTECTIONS				
Parameter		Туре		Value
Input Fuse (5)		internal fusible resistor,		ible resistor, 1Ω/1W
Short Circuit Protection (SCP)	be	low 100mΩ	contir	nuous, auto recovery
Over Voltage Category				OVCII
Over Current Protection (OCP)		3.3Vout 5Vout 12Vout 24Vout		hiccup mode
Class of Equipment				Class II
Isolation Voltage (6)	I/P to O/P	rated for 1 minute		3kVAC
Isolation Resistance				100M Ω min.
Isolation Capacitance				1nF
Insulation Grade				reinforced
Leakage Current		I/P to O/P		0.25mA max.


Notes:

Note5: Refer to local safety regulations if input over-current protection is also required

Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage

Note7: For operation at 230VAC, an external MOV is recommended. The Varistor should comply with IEC-61051-2. e.g. EPCOS S14 series

Protection Circuit





Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)

ENVIRONMENTAL				
Parameter	Condit	ion		Value
On avating Tampagatura Danga	@ natural convention 0.1 m/s	full	load	-25°C to +70°C
Operating Temperature Range	@ natural convection 0.1m/s	refer to "Dera	ating Graph"	-25°C to +80°C
Maximum Case Temperature				+120°C
Temperature Coefficient				0.03%/K
Operating Altitude (8)				4000m
Operating Humidity	non-conde	ensing		10% - 95% RH max.
Pollution Degree				PD2
Shock				10-150Hz, 2G 10min./1cycle, period 60min. each along x,y,z axes
Vibration	according to MIL	-STD-202G		20G/11ms pulse, 3 times at each x, y, z axes
MTBF (9)	according to MIL UDDV 017	E mothod 2	+25°C	1691 x 10 ³ hours
IVITOF 17	according to MIL-HDBK-217	r, memou Z	+70°C	424 x 10 ³ hours

Notes:


Note8: Recognized by UL for safe operation up to 4000m. High altitude operation may impact the performance and lifetime.


Contact TechsupportAT@RECOM-POWER.com for advice

Note9: Based on calculation for 5Vout

Derating Graph

(@ Chamber and natural convection 0.1 m/s)





SAFETY AND CERTIFICATIONS Certificate Type (Safety)	Report / File Number	Standard
Information Technology Equipment, General Requirements for Safety	SA1804152L01001	IEC60950-1:2005 2nd Edition + Am2:2013 EN60950-1:2006 + A12:2011 + A2:2013
Audio/Video, information and communication technology equipment - Part1: Safety requirements	E196683-A5 and E19668-A6001	UL62368-1, 2nd Edition CAN/CSA-C22.2 No. 62368-1-14
Audio/Video, information and communication technology equipment - Part1: Safety requirements (CB Scheme)	0440044500 004	IEC62368-1:2014 2nd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements	SA1804152S 001	EN62368-1:2014+A11:2017
RoHS2		RoHS 2011/65/EU + AM2015/863



Series


Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)


EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment - Emission requirements		EN55032, Class B
Information technology equipment - Immunity characteristics - Limits and methods of measurement	EA1804152E 01001	EN55024:2010 + A1:2015
ESD Electrostatic discharge immunity test	Air ±2, 4, 8kV Contact ±2, 4kV	EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3:2006 + A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: ±1.0kV	EN61000-4-4:2012, Criteria A
Surge Immunity	AC Power Port: L-N ±1.0kV	EN61000-4-5:2014, Criteria B
Immunity to conducted disturbances, induced by radio-frequency fields	AC Power Port 3V	EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	50Hz, 1A/m	EN61000-4-8:2009, Criteria A
	Voltage Dips >95%	EN61000-4-11:2004, Criteria A
Voltage Dips and Interruption	Voltage Dips 30%	EN61000-4-11:2004, Criteria B
	Voltage Interruptions >95%	EN61000-4-11:2004, Criteria B
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013


DIMENSION AND PHYSICAL CHARACTERISTICS


DIMENSION AND THIS IS A CONTROL OF THE THORSE			
Parameter	Туре	Value	
Material	case	black plastic (UL94V-2)	
Waterial	PCB	FR4 (UL94V-0)	
Dimension (LxWxH)		33.7 x 22.2 x 19.0mm	
Weight		12g typ.	

Dimension Drawing (mm)









Recommended Footprint Details

	110001111110114041 001	print Botano
	2.54	
2.54		30
- - -	Top Vi	ew 4
_ _ _	1 01	
-		

Pin Connections

Pin #	Single
1	VAC in (L)
2	VAC in (N)
3	-Vout
4	+Vout

Tolerance: Pin length: -0.5/+0.9xx.x= ± 0.5 mm

 $x.x = \pm 0.511111$ $x.xx = \pm 0.25$ mm



Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)

PACKAGING INFORMATION			
Parameter	Туре	Value	
Packaging Dimension (LxWxH)	tube	470.0 x 36.4 x 26.4mm	
Packaging Quantity		20pcs	
Storage Temperature Range		-25°C to +85°C	
Storage Humidity	non-condensing	5% - 95% RH max.	

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

www.recom-power.com REV.: 2/2019 PA-6