

## PCBN clamp holder, negative, left

For longitudinal turning using CN indexable insert

**ATORN**<sup>®</sup>

### Application

For longitudinal turning using CN indexable insert 80°.

### Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type C, 75° pitch angle, 80° tip angle, 0° clearance angle

### Advantage

- extremely stable geometry for longitudinal machining with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths



<b>Art. No.</b>	<b>17837 121</b>
<b>ISO name</b>	PCBN R/L 2525 M16
<b>Shaft height</b>	25 mm
<b>Shank width</b>	25 mm
<b>Length</b>	150 mm
<b>Length of head</b>	34 mm
<b>Programming size</b>	22 mm
<b>Suitable for indexable inserts</b>	CN.. 1606..
<b>Tool design</b>	Left
<b>DIN</b>	4983

### EAN-Code

4050293347920