

5499910-6 ✓ ACTIVE



## AMP-LATCH | AMP-LATCH Universal Headers


TE Internal #: 5499910-6

AMP-LATCH Universal Headers, Ribbon Cable Connectors, Wire-to-Board, 26 Position, 2.54mm [.1in] Centerline, Vertical, Through Hole - Solder

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors >

### AMP-LATCH UNIVERSAL HEADERS



Connector System: **Wire-to-Board**

Number of Positions: **26**

Centerline (Pitch): **2.54 mm [.1 in]**

PCB Mount Retention: **Without**

PCB Mount Retention Type: **Mounting Ears**

[All AMP-LATCH UNIVERSAL HEADERS \(525\)](#)

## Features

### Product Type Features

|                                    |                                |
|------------------------------------|--------------------------------|
| Connector Type                     | Header                         |
| Ribbon Cable Connector Header Type | Universal Ejection Pin Headers |
| Connector Mating Latch & Lock Type | Short                          |
| Connector Product Type             | Connector Assembly             |
| Connector System                   | Wire-to-Board                  |
| Connector & Housing Type           | Plug                           |
| Connector & Contact Terminates To  | Printed Circuit Board          |

### Configuration Features

|                       |          |
|-----------------------|----------|
| Number of Positions   | 26       |
| PCB Mount Orientation | Vertical |
| Number of Rows        | 2        |

### Electrical Characteristics



|                       |         |
|-----------------------|---------|
| Insulation Resistance | 5000 MΩ |
| Operating Voltage     | 250 VAC |

### Body Features

|                   |          |
|-------------------|----------|
| Connector Profile | Standard |
|-------------------|----------|

### Contact Features

|   |                        |
|---|------------------------|
| Mating Square Post Dimension                            | .64 mm[.025 in]        |
| PCB Contact Termination Area Plating Material Thickness | 2.54 μm[100 μin]       |
| Contact Type  | Pin                    |
|   | 15 μin                 |
| Contact Mating Area Plating Material                    | Gold                   |
| Contact Shape & Form                                    | Square                 |
| PCB Contact Termination Area Plating Material           | Tin                    |
| Contact Base Material                                   | Brass, Phosphor Bronze |
| Contact Current Rating (Max)                            | 1 A                    |

### Termination Features

|   |                       |
|---|-----------------------|
| Round Termination Post & Tail Diameter      | .64 mm[.025 in]       |
| Termination Post & Tail Length              | 2.79 mm[.11 in]       |
| Termination Method to Printed Circuit Board | Through Hole - Solder |

### Mechanical Attachment

|                          |                             |
|--------------------------|-----------------------------|
| Mating Alignment         | With                        |
| PCB Mount Alignment      | Without                     |
| Panel Mount Feature      | Without                     |
| PCB Mount Retention      | Without                     |
| PCB Mount Retention Type | Mounting Ears               |
| Mating Alignment Type    | Center, Dual Polarizing Bar |
| Mating Retention         | With                        |
| Mating Retention Type    | Ejection Latch              |
| Connector Mounting Type  | Board Mount                 |

### Housing Features

|                    |                              |
|--------------------|------------------------------|
| Housing Material   | Glass Filled Nylon/Polyester |
| Housing Color      | Black                        |
| Centerline (Pitch) | 2.54 mm[.1 in]               |

### Dimensions

|                             |                            |
|-----------------------------|----------------------------|
| Shrouded End Dimension      | 3.81 mm[.15 in]<br>2.06 in |
| Connector Height            | 13.94 mm[.549 in]          |
| PCB Thickness (Recommended) | 1.57 mm[.062 in]           |
| Row-to-Row Spacing          | 2.54 mm[.1 in]             |

### Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Housing Temperature Rating  | Standard                   |
| Operating Temperature Range | -65 – 105 °C[-85 – 221 °F] |

### Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

### Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

### Packaging Features

|                    |      |
|--------------------|------|
| Packaging Quantity | 24   |
| Packaging Method   | Tray |

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.  |
| Solder Process Capability                     | Wave solder capable to 265°C  |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1658622-6  
26 NOVO MIL/CTR 30DP, LEAD FREE



TE Part # 1-1658526-5  
609-2630LF FEM SOCKET, LEAD FREE



TE Part # 1658620-6  
26 NOVO MIL 15DP, LEAD FREE



TE Part # 1658621-6  
26 NOVO MIL/CTR 15DP, LEAD FREE



TE Part # 1658623-6  
26 NOVO MIL 30DP, LEAD FREE



TE Part # 1658527-9  
622-2630LF FEM SOCKET, LEAD FREE




TE Part # 1658624-6  
26 NOVO DUAL 30DP, LEAD FREE




TE Part # 1-1658528-7  
636-2630LF=FEM SKT BLADE POL 1

## Also in the Series | AMP-LATCH Universal Headers



Ribbon Cable Connectors(525)



Ribbon Connector Accessories(14)

## Customers Also Bought




TE Part #2-5748003-0  
D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mm



TE Part #194002-1  
PIN ASSY..070



TE Part #770262-3  
06P UMNL SOK HDR ASSY 94VO LF



TE Part #1586040-2  
2P VAL-U-LOK VRT HDR W/P V0




TE Part #1761609-5  
IDC LOW PRO HDR 14P RA SHT LAT



TE Part #102312-1  
Universal Headers: Ejector Latch



TE Part #1410968-4  
MULTIGIG RT2 7RW RTM DC DF CT



TE Part #2181195-1  
C/A Nector S Plug to Pigtail LV-2 SPT-2



TE Part #2181198-4  
C/A NectorS Outlet to Pigtail LV-2 SPT-2

## Documents

### Product Drawings

[A/L UNIV HDR 26P VERT SHT LAT](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5499910-6\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5499910-6\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5499910-6\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[Ribbon Cable Interconnect Solutions](#)

English

### Product Specifications

[Product Specification](#)

English

### Product Environmental Compliance

[MD\\_5499910-6\\_061220181252\\_dmtec](#)

5499910-6

AMP-LATCH Universal Headers, Ribbon Cable Connectors, Wire-to-Board, 26  
Position, 2.54mm [.1in] Centerline, Vertical, Through Hole - Solder



English

[MD\\_5499910-6\\_061220181252\\_dmtec](#)

English