



DATA SHEET	0153006
DIN compensating cable KP 4 L-S 2x1,5 oval	valid from : 01.12.2008

Application

The compensating cable KP 4 L-S 2 x 1,5 mm² is a glass fibre insulated cable which transmits the thermoelectric voltage of PtRh/Pt thermocouples. It is for fixed installation in dry rooms and may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range. The steel wire armouring serves as mechanical protection.

Design

Conductor	1,5 mm ² (48 x 0,20 mm)
Conductor material	RCB/SCB alloying, accuracy class 2 according DIN 43722 Positive conductor: Cu (copper) Negative conductor: CuNi (cupronickel)
Core insulation	Glass fibre covering
Core identification	Positive conductor: red marked Negative conductor: white marked
Core layering	Cores parallel next to each other
Outer sheath	Glass fibre braiding with interweaved white identification thread
Armouring	Galvanized steel wire braiding with interweaved white identification thread

Electrical properties

Limiting deviation class 2 ± 60 µV (± 5,0 °C) / measuring point temperature +1000 °C

Mechanical and thermal properties

Temperature range	occasional flexing: -25 °C up to +200 °C
Minimum bending radius	occasional flexing: 15 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document: DB0153006EN	page 1 of 1
--	----------------------------	-------------