

BUILT TO PROTECT.

LEARN MORE ABOUT + OUR PRODUCTS



www.peli.com



AVAILABLE IN 18 LANGUAGES!

www.pelicatalogue.com



www.peli.com/webinars



EMEA

EUROPE, MIDDLE EAST & AFRICA HEADQUARTERS

PELI PRODUCTS, S.L.U.
C/ Provença, 388 Planta 7
08025 • Barcelona, Spain
Tel +34 934 674 999
Fax +34 934 877 393
www.peli.com

FRANCE

PELI PRODUCTS FRANCE
S.A.S.
20/22 Rue des Petits Hôtels
75010 Paris, France
Tel +33 (0)1 44 83 95 63
Fax +33 (0)1 44 83 95 68
www.peli.com

UK

PELI HARDIGG UK
Unit 4, Brookfield Industrial Estate
Leacon Road
Ashford Kent TN23 4TU
Tel + 44 (0) 1233 895 895
Fax +44 (0) 1233 895 899
www.peli.com

U.S.A.

U.S.A. & GLOBAL HEADQUARTERS

23215 Early Avenue
Torrance, CA 90505 USA
Tel 310.326.4700
800.473.5422 (Outside CA)
Fax 310.326.3311
www.pelican.com

GERMANY

PELI PRODUCTS GERMANY GmbH
Düsseldorf Kö-Bogen
Business Center
Königsallee 2b, 5th Floor
40212 Düsseldorf, Germany
Tel +49 (0) 211 882 42 401
Fax +49 (0) 211 882 42 200
www.peli.com

UAE

PELICAN PRODUCTS FZE
JAFZA One Building A office 1511/1512
Jebel Ali Free Zone gate 5
P.O.Box 261008
Dubai – United Arab Emirates
Tel +971 4 8876550
Fax +971 4 8876549
www.pelican.com
www.peli.com

PELICAN HARDIGG

147 North Main Street
South Deerfield, MA 01373
Tel (800) 542 73 44
Fax (413) 665 8330
www.pelican.com

* We also have offices in Canada, Japan, China, Australia, South Korea and India

PELI LIMITED LIFETIME* WARRANTY

Peli Products, S.L.U. ("Peli") guarantees its lights and headlamps for a lifetime* against breakage or defects in workmanship. This guarantee does not cover the lamp or batteries. All warranty claims of any nature are barred if the product has been altered, damaged or in any way physically changed, or subjected to abuse, misuse, negligence or accident. For complete warranty details, see www.peli.com/warranty

* Lifetime guarantee not applicable where prohibited by law.



PELI™ LIGHTS CATALOGUE



HIGH OUTPUT
LEDs



SAFETY APPROVED
MODELS



RECHARGEABLE
MODELS

Follow us on:



©2017 Peli Products, S.L.U. All trademarks are registered and/or unregistered trademarks of Pelican Products, Inc., its subsidiaries and/or affiliates. All details included in this catalogue are correct when printed but for most updated information please visit www.peli.com and www.pelicatalogue.com.
Part No. 0030-000-501E JAN 17



Check out our 40 Years
of Protection video:



LIFETIME GUARANTEE* - PROVEN FOR OVER 40 YEARS

TABLE + OF CONTENTS

| | |
|--|--------------|
| PERFORMANCE | 3 |
| SAFETY | 4-5 |
| PELI LIGHTS | |
| Small Lights | 6-7 |
| Medium Lights | 8-10 |
| Large Lights | 11 |
| Atex Lights | 12-15 |
| Tactical Lights | 16-17 |
| Headlights | 18-19 |
| Right Angle | 20 |
| Light Mounting Systems & Holsters | 21 |
| Specifications | 22-24 |
| CUSTOM LABELS & PELI LIGHTING TOOLS | 25 |
| FULL LINE OVERVIEW | 26-27 |



Uros Podlogar, professional photographer

PERFORMANCE

+ STANDARDS AND RATINGS (Applicable to torches only)




LIGHT OUTPUT

Light Output is the total luminous flux. It is the total quantity of emitted overall light energy as measured by integrating the entire angular output of the portable light source. Light output in this standard is expressed in units of lumens.



PEAK BEAM INTENSITY

Peak Beam Intensity is the maximum luminous intensity typically along the central axis of a cone of light. The value is reported in candela and does not change with distance.




RUN TIME

Run Time is defined as the duration of time from the initial light output value – defined as 30 seconds after the point the device is first turned on – using fresh batteries, until the light output reaches 10% of the initial value.



WATER RESISTANT

Water Resistant – IPX4 Water splashed against the device from any direction shall have no harmful effects.



BEAM DISTANCE

Beam Distance is defined as the distance from the device at which the light beam is 0.25 lux (0.25 lux is approximately the equivalent of the light emitted from the full moon "on a clear night in an open field").



WATER PROOF/SUBMERSIBLE

Water Proof // IPX7 – Ingress of water in quantities causing harmful effects shall not be possible when the enclosure is temporarily immersed in water under standardized conditions of pressure and time.
Submersible // IPX8 – Ingress of water in quantities causing harmful effects shall not be possible when the enclosure is continuously immersed in water under conditions which shall be stated by manufacturer, but which are more severe than for IPX7.

ANSI STANDARDS □ (AMERICAN NATIONAL STANDARDS INSTITUTE)

Why create standards? While Peli was one of the first manufacturers to use quantifiable test procedures, the need was recognised to develop a common language that customers could use to select the right torch for their specific needs. As a result, the American National Standards Institute (ANSI), with input from the torch industry, developed performance standards and symbols to effectively communicate a light's features and benefits. The Resulting ANSI/NEMA FL 1 Standards include the following six criteria.

+ GLOSSARY OF TERMS

CANDELA A unit of measurement of the intensity of light that is emitted by a light source in a particular direction.

LUX The unit of luminous flux in the International System, equal to the amount of light given out through a solid angle by a source of one candela intensity radiating equally in all directions.

LUMEN A unit of measurement of the amount of brightness that comes from a light source. Lumens define "luminous flux," which is energy within the range of frequencies we perceive as light.

INTEGRATING SPHERE An integrating sphere is a measurement device with an entrance port that can accept all the directional light output of the device under test, or can totally enclose the device itself. The walls of the sphere should be highly diffuse with high reflectivity (>80%) and the spectroradiometer should be shielded from direct view of the device under test by a baffle system.

IP (INGRESS PROTECTION) – These ratings specify the environmental protection the enclosure provides. The IP rating normally has two numbers (IPXX).

The first number represents protection from solid objects or materials (dust) where as the second number represents protection from liquids (water). With the IP rating IP 54, 5 describes the level of protection from solid objects and 4 describes the level of protection from liquids as described by the IP Rating System (Solids vary from 0-6 IP rating , Liquids vary from 0-8 IP rating).

RECHARGEABLE Denotes a torch which contains rechargeable batteries and charging station. These models are shown with the rechargeable icon.



SAFETY

IS MY TORCH CORRECTLY CERTIFIED BY ATEX?

Photo by Ricardo Alves

To meet the exacting requirements of ATEX directive 2014/34/EU, Peli Lights are tested to ensure that they pose no threat of ignition when operating within hazardous locations. Using approved laboratories, the lights are tested to ensure that they will withstand rigorous impact and drop tests, severe environmental exposure and meet a minimum of IP54 water and dust ingress protection. Longevity and safety are assured by design. Each light certified by ATEX should have a code printed on its body. This code advises the user as to the area in which it can be safely used without risk of explosion.

Need more information about ATEX? Please visit www.peli.com

CE Ex II 1 G Ex ia op is IIC T6/T4 Ga

ATEX code corresponding to the 1930Z0 torch



+ COMPARISON TABLE US (UL, FM) AND EUROPEAN (ATEX) CLASSIFICATION


| HAZARDOUS AREA ELECTRICAL GUIDELINES | | | | | |
|--------------------------------------|--|--|--------------------------------|---------------------------------------|-------------------------|
| | SUBSTANCE | TYPICAL ENVIRONMENTS | US CLASSIFICATIONS | EUROPEAN CLASSIFICATION | VOLATILITY* |
| CLASS I | Flammable Gasses, Vapors or Liquids (Acetylene, Hydrogen, Ethylene, Propane) | <ul style="list-style-type: none"> - Oil Refinery - - Paint Warehouse - - Offshore Oil Rig - - Spray Booth - | Division 1 (Hazard Likely) | Category 1 / Zone 0 (Hazard Certain) | MOST ↑ ↓ LEAST |
| | | | Division 2 (Hazard Not Likely) | Category 2 / Zone 1 (Hazard Likely) | |
| CLASS II | Combustible Dusts (Metals [Div.1 only], Coal, Grain) | <ul style="list-style-type: none"> - Coal Mine - - Grain Silo - - Munitions Factory - - Hay Storage Facility - | Division 1 (Hazard Likely) | Category 1 / Zone 20 (Hazard Certain) | |
| | | | Division 2 (Hazard Not Likely) | Category 2 / Zone 21 (Hazard Likely) | |
| CLASS III | Ignitable Fibers & Flyings (Machined Magnesium) | <ul style="list-style-type: none"> - Paper Mill - - Woodworking Facility - - Textile Mill - - Cotton Gin - | Division 1 (Hazard Likely) | N/A | |
| | | | Division 2 (Hazard Not Likely) | N/A | |

* A torch certified to Category 1 (Zone 0) is safe for use in areas rated Category 2 (Zone 1) and Category 3 (Zone 2). Conversely the opposite is not possible. This information should be taken only as a guideline. Contact us for specific details on both, US and European Directives.

| US CLASSIFICATIONS | | EUROPEAN CLASSIFICATIONS | |
|--|--|---|---|
| Division 1: Where volatile substances can exist all of the time or some of the time under normal operating conditions. | Division 2: Where volatile substances are not likely to exist under normal operating conditions. | Category 1 / Zone 0: Flammable material present for long periods (more than 1.000 hours* a year). | Category 3 / Zone 2: Flammable material present for short periods (less than 10 hours* a year). |
| | | Category 2 / Zone 1: Flammable material present in normal operation (10- 1.000 hours* a year). | |

* These hours are guidelines adopted by various organisations. They are not coming from official ATEX sources.

+ DIAGRAM OF CLASS / DIVISIONS / ZONES



SMALL LIGHTS

When compact is a must or just a convenience, choose from Peli's range of powerful lights. Whether composite or alloy, certified or coloured, you'll find the perfect model for your next job.



1810

LIGHT SOURCE//
LED

BATTERIES//
4 LR 41 Alkaline (included)

LENGTH//
3.8 cm (1.50")

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
16
RUN TIME
8h 30m

MITYLITE™ 1900Z1

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
2 AAA Alkaline (included)

LENGTH//
10.4 cm (4.09")

CERTIFICATIONS//
II 2 G Ex e ib IIB T4 Gb, II 2 D Ex ib IIIC T100°C Db

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
11
RUN TIME
1h 30m

MITYLITE™ 1900

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
2 AAA Alkaline (included)

LENGTH//
10.4 cm (4.09")

CERTIFICATIONS//
CI, D1/CI1, D2

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
11
RUN TIME
1h 30m

1910

LIGHT SOURCE//
LED

BATTERIES//
1 AAA Alkaline (included)

LENGTH//
9.7 cm (3.8")

MODES//
High / Low

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
72
RUN TIME
4h

1920

LIGHT SOURCE//
LED

BATTERIES//
2 AAA Alkaline (included)

LENGTH//
14.0 cm (5.5")

MODES//
High / Low

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
120
RUN TIME
8h 30m

L1™ 1930Z0

LIGHT SOURCE//
LED

BATTERIES//
4 LR 44 Alkaline (included)

LENGTH//
6.7 cm (2.64")

CERTIFICATIONS//
II 1 G Ex ia op is IIC T6/T4 Ga

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
12
RUN TIME
4h 15m

VB3™ 2220Z1

LIGHT SOURCE//
LED

BATTERIES//
2 CR2032 Lithium (included)

LENGTH//
8.9 cm (3.50")

CERTIFICATIONS//
II 2 G Ex ib op is IIC T6 Gb

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
9
RUN TIME
34h

MITYLITE™ 2340

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
2 AA Alkaline (not included)

LENGTH//
15.9 cm (6.25")

CERTIFICATIONS//
CI II, D2

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
10
RUN TIME
4h 30m

L1™ 1930

LIGHT SOURCE//
LED

BATTERIES//
4 LR 44 Alkaline (included)

LENGTH//
6.7 cm (2.64")

CERTIFICATIONS//
CI, D1/CI1, D2

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
12
RUN TIME
4h 15m

MITYLITE™ 1965Z0

LIGHT SOURCE//
LED

BATTERIES//
2 AAA Alkaline

LENGTH//
13.9 cm (5.48")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T90°C Da

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
34
RUN TIME
3h 45m

MITYLITE™ 2300

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
2 AA Alkaline (included)

LENGTH//
14.3 cm (5.62")

CERTIFICATIONS//
CI, D1/CI1, D2

■ ■ ■ ■ ■ ■ ■ ■



LUMENS
11
RUN TIME
4h 30m



MEDIUM LIGHTS

Nothing beats the versatility of a hand-held light. Easy to carry, stash in a pocket, or clip to a helmet, these lights do just about everything. And when hazardous areas are present, you can count on Peli's line of safety certified lighting tools. You'll even find photoluminescent models with "glow-in-the-dark" material to help you find your torch in an emergency.



PELILITE™ 1800

LIGHT SOURCE//
Incandescent (Xenon)
BATTERIES//
2 C Alkaline (not included)
LENGTH//
15.2 cm (6")
CERTIFICATIONS//
Cl II, D2



SABRELITE™ 2000

LIGHT SOURCE//
Incandescent (Xenon)
BATTERIES//
3 C Alkaline (not included)
LENGTH//
19.8 cm (7.79")
CERTIFICATIONS//
Cl, D1/CII, D2



Photoluminescent
2003PL Shroud

SABRELITE™ 2000Z1

LIGHT SOURCE//
Incandescent (Xenon)
BATTERIES//
3 C Alkaline (not included)
LENGTH//
19.8 cm (7.79")
CERTIFICATIONS//
II 2 G Ex e ib IIC T4 Gb, II 2 G Ex e ib IIC T150°C Gb



Photoluminescent
2003PL Shroud

SABRELITE™ 2010

LIGHT SOURCE//
LED
BATTERIES//
3 C Alkaline (not included)
LENGTH//
20.6 cm (8.11")
CERTIFICATIONS//
Cl II III, D1



Photoluminescent
2013PL Shroud

SABRELITE™ 2010Z0

LIGHT SOURCE//
LED

BATTERIES//
3 C Alkaline (not included)

LENGTH//
20.6 cm (8.11")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 T3 Ga, II 1 D ia IIC T135c T200c Da IP6X



Photoluminescent
2013PL Shroud

STEALTHLITE™ 2400Z1

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
4 AA Alkaline (included)

LENGTH//
16.5 cm (6.49")

CERTIFICATIONS//
II 2 G Ex e ib IIC T4 Gb



STEALTHLITE™ 2400

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
4 AA Alkaline (included)

LENGTH//
16.5 cm (6.49")

CERTIFICATIONS//
Cl, D1/CII, D2



STEALTHLITE™ 2410 LED

LIGHT SOURCE//
LED

BATTERIES//
4 AA Alkaline (included)

LENGTH//
17.8 cm (7")

CERTIFICATIONS//
Cl II III, D1



STEALTHLITE™ 2410Z0

LIGHT SOURCE//
LED

BATTERIES//
4 AA Alkaline (included)

LENGTH//
17.8 cm (7")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIC T135°C Da



STEALTHLITE™ 2450

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
4 NiMH (included)

LENGTH//
16.5 cm (6.5")

CERTIFICATIONS//
Cl II, D2



STEALTHLITE™ 2460

LIGHT SOURCE//
LED

BATTERIES//
4 NiMH (included)

LENGTH//
17.8 cm (7")

CERTIFICATIONS//
Cl II, D2



STEALTHLITE™ 2460Z1

LIGHT SOURCE//
LED

BATTERIES//
4 NiMH (included)

LENGTH//
17.8 cm (7")

CERTIFICATIONS//
II 2 G Ex ib IIC T4 Gb



*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

THE SABRELITE ALLOWED ME TO SAVE ANOTHER LIFE

Some months ago, while at a fire, I accidentally dropped my light between a wall space. It fell about 5 to 6 meters before hitting the concrete floor below. To my relief there just happened to be an opening in the base of the wall where my SabreLite landed. It was still shining when I picked it up, and after a quick inspection I couldn't find a thing wrong with it. After this I carried searching the bedrooms of the house where I found an elderly lady whom we successfully removed from the house. I was amazed because I feel that the quality of the light allowed me to save the life of another human being.

François Gireau, professional firefighter Paris area



3315Z0

LIGHT SOURCE//
LED
BATTERIES//
3 AA Alkaline (included)
LENGTH//
15.6 cm (6.14")
CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga,
II 1 D Ex ia IIIC T130°C Da



3315RZ1-RA

NON-ATEX VERSION
COMING SOON

LIGHT SOURCE//
LED
BATTERIES//
Lithium-Ion (included)
LENGTH//
21 cm (8.27")
CERTIFICATIONS//
II 2G Ex ib op is IIC T4 Gb
MODES//
High / Low / Flashing



NEW



3310PL PHOTOLUMINESCENT

LIGHT SOURCE//
LED

BATTERIES//
3 AA Alkaline (included)

LENGTH//
15.6 cm (6.14")

MODES//
High / Low / Flashing
(torch body glows in the dark)

(Photoluminescent)



3310 ELS (EMERGENCY LIGHTING SYSTEM)

LIGHT SOURCE//
LED

BATTERIES//
3 AA Alkaline (included)

LENGTH//
15.6 cm (6.14")

INCLUDES//
3310PL and Wall Mountable Case
(torch body glows in the dark)

(Photoluminescent)



3315RZ1

NON-ATEX VERSION
COMING SOON

LIGHT SOURCE//
LED

BATTERIES//
Lithium-Ion (included)

LENGTH//
15.5 cm (6.11")

CERTIFICATIONS//
II 2G Ex ib op is IIC T4 Gb

MODES//
High / Low / Flashing




3325Z0

LIGHT SOURCE//
LED

BATTERIES//
3 AA Alkaline (included)

LENGTH//
15.4 cm (6.06")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga



LARGE LIGHTS

Colossal performance with lightweight designs. Features such as full time battery level indication, articulating light head and multiple light modes keep you in control of the job. Peli is also a leader of high performance lithium-ion technology in portable lighting.




9410L LED LANTERN

LIGHT SOURCE//
LED

BATTERIES//
Lithium-Ion (included)

LENGTH//
22.2 cm (8.75")

MODES//
High / Low / Flashing
Full Time Battery Indicator




9415Z0 LED LANTERN

LIGHT SOURCE//
LED

BATTERIES//
4 C NiMH (included)

LENGTH//
22.2 cm (8.75")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga



*For more information on the ATEX Zone 0 & 1 lights, see page 4-5


*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

ATEX LIGHTS



Zone 0 & 1 (Cat. 1 & 2)

Peli's extense range of Zone 0 and Zone 1 torches complies with the highest standards of the ATEX Directive and meet the IEC (International Electrotechnical Commission) requirements. Designed for use in hazardous areas, professionals working in the pharmaceutical, fire and rescue, hazmat and other high-risk industries can be confident that Peli offers the safety approvals needed for a large variety of risky situations.



PELI ATEX LIGHTS

PELI ATEX LIGHTS

MITYLITE™ 1900Z1

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
2 AAA Alkaline (included)

LENGTH//
10.4 cm (4.09")

CERTIFICATIONS//
II 2 G Ex e ib IIB T4 Gb, II 2 D Ex ib IIIC T100°C Db



LUMENS
11
RUN TIME
1h 30m

L1™ 1930Z0

LIGHT SOURCE//
LED

BATTERIES//
4 LR 44 Alkaline (included)

LENGTH//
6.7 cm (2.64")

CERTIFICATIONS//
II 1 G Ex ia op is IIC T6/T4 Ga



LUMENS
12
RUN TIME
4h 15m

MITYLITE™ 1965Z0

LIGHT SOURCE//
LED

BATTERIES//
2 AAA Alkaline

LENGTH//
13.9 cm (5.48")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T90°C Da



LUMENS
34
RUN TIME
3h 45m

SABRELITE™ 2000Z1

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
3 C Alkaline (not included)

LENGTH//
19.8 cm (7.79")

CERTIFICATIONS//
II 2 G Ex e ib IIC T4 Gb, II 2 G Ex e ib IIC T150°C Gb



LUMENS
39
RUN TIME
6h



Photoluminescent
2003PL Shroud

SABRELITE™ 2010Z0

LIGHT SOURCE//
LED

BATTERIES//
3 C Alkaline (not included)

LENGTH//
20.6 cm (8.11")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 T3 Ga, II 1 D Ex ia IIIC T135°C T200°C Da IP6X



LUMENS
129
RUN TIME
22h



Photoluminescent
2013PL Shroud

STEALTHLITE™ 2400Z1

LIGHT SOURCE//
Incandescent (Xenon)

BATTERIES//
4 AA Alkaline (included)

LENGTH//
16.5 cm (6.49")

CERTIFICATIONS//
II 2 G Ex e ib IIC T4 Gb



LUMENS
38
RUN TIME
4h 30m


STEALTHLITE™ 2460Z1

LIGHT SOURCE//
LED

BATTERIES//
4 AA NiMH (included)

LENGTH//
17.8 cm (7")

CERTIFICATIONS//
II 2 G Ex ib IIC T4 Gb



LUMENS
181
RUN TIME
5h


HEADSUP LITE™ 2610Z0

LIGHT SOURCE//
LED

BATTERIES//
3 AAA Alkaline (included)

LENGTH//
3.8 cm (1.49")

CERTIFICATIONS//
II 1 G Ex ia op is IIC T4 Ga



LUMENS
30
RUN TIME
47h

VB3™ 2220Z1

LIGHT SOURCE//
LED

BATTERIES//
2 CR2032 Lithium (included)

LENGTH//
8.9 cm (3.50")

CERTIFICATIONS//
II 2 G Ex ib op is IIC T6 Gb



LUMENS
9
RUN TIME
34h

STEALTHLITE™ 2410Z0

LIGHT SOURCE//
LED

BATTERIES//
4 AA Alkaline (included)

LENGTH//
17.8 cm (7")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T135°C Da



LUMENS
153
RUN TIME
5h 45m



*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

*For more information on the ATEX Zone 0 & 1 lights, see page 4-5


HEADSUP LITE™ 2690Z0

LIGHT SOURCE//
LED

BATTERIES//
3 AAA Alkaline (included)

LENGTH//
7.1 cm (2.81")

CERTIFICATIONS//
I M1 Ex ia I Ma, II 1 G Ex ia IIC T4 Ga,
II 1D Ex ia IIIC T65°C Da



HEADSUP LITE™ 2755Z0

LIGHT SOURCE//
LED

BATTERIES//
3 AAA Alkaline (included)

LENGTH//
5.7 cm (2.25")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga

MODES//
High / Low / Flashing



HEADSUP LITE™ 2785Z1

LIGHT SOURCE//
LED

BATTERIES//
4 AA Alkaline (included)

LENGTH//
7.6 cm (3.00")

CERTIFICATIONS//
II 2 G Ex ia IIC T4 Gb

MODES//
High / Medium / Low / Downcast / Spot / Flashing



3315RZ1

NON-ATEX VERSION
COMING SOON



LIGHT SOURCE//
LED

BATTERIES//
Lithium-Ion

LENGTH//
15.5 cm (6.11")

CERTIFICATIONS//
II 2G Ex ia op is IIC T4 Gb

MODES//
High / Low / Flashing



HEADSUP LITE™ 2745Z0


LIGHT SOURCE//
LED

BATTERIES//
3 AAA Alkaline (included)

LENGTH//
5.7 cm (2.25")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga

MODES//
High / Low



HEADSUP LITE™ 2765Z0

LIGHT SOURCE//
LED

BATTERIES//
3 AAA Alkaline (included)

LENGTH//
5.7 cm (2.25")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga



3315Z0

LIGHT SOURCE//
LED

BATTERIES//
3 AA Alkaline (included)

LENGTH//
15.6 cm (6.14")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga,
II 1 D Ex ia IIIC T130°C Da



3315RZ1-RA

NON-ATEX VERSION
COMING SOON



LIGHT SOURCE//
LED

BATTERIES//
Lithium-Ion (included)

LENGTH//
21 cm (8.27")

CERTIFICATIONS//
II 2G Ex ia op is IIC T4 Gb

MODES//
High / Low / Flashing



3325Z0

LIGHT SOURCE//
LED

BATTERIES//
3 AA Alkaline (included)

LENGTH//
15.4 cm (6.06")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga



LITTLE ED™ 3660Z1

LIGHT SOURCE//
LED

BATTERIES//
4 AA NiMH (included)

LENGTH//
19.1 cm (7.51")

CERTIFICATIONS//
II 2 G Ex ia IIC T4 Gb



3765Z0

LIGHT SOURCE//
LED

BATTERIES//
4 AA NiMH

LENGTH//
13.6 cm (5.36")

CERTIFICATIONS//
II 1 G Ex ia op is IIC T3 Ga

MODES//
High / Low / Downcast



LITTLE ED™ 3610Z0

LIGHT SOURCE//
LED

BATTERIES//
4 AA Alkaline (included)

LENGTH//
19.1 cm (7.51")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T135°C Da



3715Z0

LIGHT SOURCE//
LED

BATTERIES//
4 AA Alkaline

LENGTH//
13.6 cm (5.36")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T130c Da

MODES//
High / Low / Downcast



Photoluminescent
3713PL Shroud

9415Z0 LED LANTERN

LIGHT SOURCE//
LED

BATTERIES//
4 C NiMH (included)

LENGTH//
22.2 cm (8.75")

CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga



THE PELI 3715Z0 IS AN ABSOLUTE FAVOURITE

SURVIVAL + STORIES

Compact and it really packs a lot of light. The three types of light are really convenient for different purposes. For instance, the large light to explore incidents and the three small LED lights to read maps or walk in dark areas. I also use this light to train in our hazmat suits. The thick rubber gloves are not an issue when working with the light. The button on top is really good to operate and the grip on the side helped me during the training. This light is really impressive. Compared to our current lights, it really stands out!

Dutch firefighter - Fire Dpt. Brabant-Noord, Boxmeer



Guido Siebers

*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

TACTICAL LIGHTS

Peli's tactical lights are field ready and built to withstand the hard knocks that come with the job. The lights are presented pre-focused to provide a beam of very bright central light and long-range, surrounded by one of lower intensity for better peripheral vision.

PELI TACTICAL LIGHTS

PELI TACTICAL LIGHTS

2350



LIGHT SOURCE//
LED
BATTERIES//
1 AA Alkaline (included)
LENGTH//
10.7 cm (4.23")
MODES//
High / Strobe / Low

LUMENS
100
UP TO
RUN TIME
15h

2370



LIGHT SOURCE//
LED
BATTERIES//
2 AA Alkaline (included)
LENGTH//
16.3 cm (6.43")
MODES//
High / Low / Red / Blue

LUMENS
106
UP TO
RUN TIME
41h 15m

2360 LED



LIGHT SOURCE//
LED
BATTERIES//
2 AA Alkaline (included)
LENGTH//
15.7 cm (6.2")
MODES//
High / Strobe / Low

LUMENS
375
UP TO
RUN TIME
13h

2380



LIGHT SOURCE//
LED
BATTERIES//
2 AA Alkaline (included)
LENGTH//
16.4 cm (6.44")
MODES//
High / Low / Spot To Flood

LUMENS
159
UP TO
RUN TIME
13h

2380R



LIGHT SOURCE//
LED
BATTERIES//
Lithium-Ion (included)
LENGTH//
16.5 cm (6.48")
MODES//
High / Strobe / Low / Spot To Flood

LUMENS
305
UP TO
RUN TIME
25h

USB

7060



LIGHT SOURCE//
LED
BATTERIES//
Lithium-Ion (included)
LENGTH//
22 cm (8.65")
MODES//
High / Strobe / Medium / Low / Self Programmable

LUMENS
368
UP TO
RUN TIME
45h

7600



LIGHT SOURCE//
LED
BATTERIES//
Lithium-Ion (included)
LENGTH//
15.7 cm (6.19")
MODES//
High / Strobe / Medium / Low

LUMENS
944
UP TO
RUN TIME
29h

8060



LIGHT SOURCE//
LED
BATTERIES//
NiMH (included)
LENGTH//
32.2 cm (12.67")
MODES//
High / Strobe / Medium / Low / Flashing / Self Programmable

LUMENS
803
UP TO
RUN TIME
69h

7000



LIGHT SOURCE//
LED
BATTERIES//
2 CR123 Lithium-Ion (Included)
LENGTH//
13.5 cm (5.31")
MODES//
High / Strobe / Medium / Low / Self Programmable

LUMENS
602
UP TO
RUN TIME
16h

7100



LIGHT SOURCE//
LED
BATTERIES//
Lithium-Ion (included)
LENGTH//
13 cm (5.12")
MODES//
High / Strobe / Medium / Low

LUMENS
695
UP TO
RUN TIME
9h 15m

M11 8050



LIGHT SOURCE//
Incandescent (Xenon)
BATTERIES//
NiMH (included)
LENGTH//
28.6 cm (11.25")

LUMENS
164
UP TO
RUN TIME
2h 15m



HEADLAMPS

With up to 558 lumens, revolutionary downcast lighting, USB charging and battery level indication, these headlamps are packed with features. Other options, including night vision friendly red illumination, interchangeable body colours and multiple settings, make these headlamps your best partner for the dark.

HEADSUP LITE™ 2610Z0

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
3.8 cm (1.49")
CERTIFICATIONS//
II 1 G Ex ia op is IIC T4 Ga



SAFETY CERTIFIED
LUMENS
30
RUN TIME
47h

HEADSUP LITE™ 2680

LIGHT SOURCE//
Recoil™ LED
BATTERIES//
4 AA Alkaline (included)
LENGTH//
11.8 cm (4.64")
CERTIFICATIONS//
CI II III, D2



SAFETY CERTIFIED
LUMENS
79
RUN TIME
10h

HEADSUP LITE™ 2690Z0

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
7.1 cm (2.81")
CERTIFICATIONS//
I M1 Ex ia I Ma, II 1 G Ex ia IIC T4 Ga,
II 1D Ex ia IIC T65°C Da



SAFETY CERTIFIED
LUMENS
74
RUN TIME
11h

2720 HEADLAMP

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
6.3 cm (2.48")
MODES//
Variable Light Output / Spot to Flood /
Red Night Vision Friendly LEDs



SAFETY CERTIFIED
LUMENS
200
RUN TIME
103h
UP TO
GESTURE ACTIVATION CONTROL

2740 HEADLAMP

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
5.7 cm (2.25")
MODES//
High / Low /
Flashing / Red LED



SAFETY CERTIFIED
LUMENS
66
RUN TIME
21h
UP TO

HEADSUP LITE™ 2745Z0

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
5.7 cm (2.25")
CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga



SAFETY CERTIFIED
LUMENS
33
RUN TIME
40h

2750 HEADLAMP

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
5.7 cm (2.25")
MODES//
High / Low / Flashing /
Red LED / Low Battery Warning
■ ■ (Photoluminescent)



SAFETY CERTIFIED
LUMENS
259
RUN TIME
11h
UP TO

HEADSUP LITE™ 2755Z0

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
5.7 cm (2.25")
CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga



SAFETY CERTIFIED
LUMENS
72
RUN TIME
15h

2760 HEADLAMP

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
5.7 cm (2.25")
MODES//
High / Medium / Low / Downcast /
Flashing / Red LED / Full-time Battery
Level Indicator
■ ■ ■ (Translucent Red)



SAFETY CERTIFIED
LUMENS
204
RUN TIME
11h
UP TO

HEADSUP LITE™ 2765Z0

LIGHT SOURCE//
LED
BATTERIES//
3 AAA Alkaline (included)
LENGTH//
5.7 cm (2.25")
CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga



SAFETY CERTIFIED
LUMENS
105
RUN TIME
9h

2780R HEADLAMP

LIGHT SOURCE//
LED
BATTERIES//
Lithium-Ion (included)
LENGTH//
7.6 cm (3.00")
MODES//
High / Medium / Low
Flashing / Downcast
Full-time Battery / Level Indicator
■ ■ ■ (Photoluminescent)
3 Interchangeable Covers Included



SAFETY CERTIFIED
LUMENS
558
RUN TIME
7h 30m
UP TO

HEADSUP LITE™ 2785Z1

LIGHT SOURCE//
LED
BATTERIES//
4 AA Alkaline (included)
LENGTH//
7.6 cm (3.00")
CERTIFICATIONS//
II 2 G Ex ib IIC T4 Gb
MODES//
High / Medium / Low / Downcast / Spot / Flashing



SAFETY CERTIFIED
LUMENS
215
RUN TIME
98h



PELI HEADLAMPS

*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

RIGHT ANGLE LIGHTS

Firefighters put everything on the line and the correct lighting tools are critical. Right angle (90°) torches often worn on turnout coats offer hands-free performance. With extreme peak beam intensity and smoke-cutting penetration, these lights will get you in and out of tough situations safely.



VERSABRITE™ 2250

LIGHT SOURCE//
Incandescent (Xenon)
BATTERIES//
2 AA Alkaline (included)
LENGTH//
9.8 cm (3.87")
CERTIFICATIONS//
CI II, D2




LITTLE ED™ 3610Z0

LIGHT SOURCE//
LED
BATTERIES//
4 AA Alkaline (included)
LENGTH//
19.1 cm (7.51")
CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T135°C Da



3715Z0

LIGHT SOURCE//
LED
BATTERIES//
4 AA Alkaline
LENGTH//
13.6 cm (5.36")
CERTIFICATIONS//
II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T130c Da
MODES//
High / Low / Downcast



Photoluminescent
3715PL Shroud

3315RZ1-RA

LIGHT SOURCE//
LED
BATTERIES//
Lithium-Ion (included)
LENGTH//
21 cm (8.27")
CERTIFICATIONS//
II 2G Ex ib op is IIC T4 Gb



NEW

LITTLE ED™ 3660Z1

LIGHT SOURCE//
LED
BATTERIES//
4 AA NIMHA (included)
LENGTH//
19.1 cm (7.51")
CERTIFICATIONS//
II 2 G Ex ib IIC T4 Gb



3765Z0

LIGHT SOURCE//
LED
BATTERIES//
4 AA NIMH
LENGTH//
13.6 cm (5.36")
CERTIFICATIONS//
II 1 G Ex ia op is IIC T3 Ga
MODES//
High / Low / Downcast




LIGHT MOUNTING SYSTEMS AND HOLSTERS



CAT. NO. 610

FRONT SIGHT MOUNT
Fits Peli Lights - 2320, 2330, 2390, 7000. Includes Remote Pressure Switch. For use with: AR15, M16, and M4 Carbine (special orders only).



CAT. NO. 620

SIDE SLING MOUNT
Fits Peli Lights - 2320, 2330, 2390, 7000. Includes Remote Pressure Switch. For use with: AR15, M16, and M4 Carbine (special orders only).



CAT. NO. 630

FOREGRIP MOUNT
Fits Peli Lights - 2320, 2330, 2390, 7000. Includes Remote Pressure Switch. For use with: Heckler, and Koch MP5 (special orders only).



CAT. NO. 2326

REMOTE PRESSURE SWITCH
Our tactical pressure switch replaces the standard tailcap on the torch. A 6" cord attached to a 2" pressure-sensitive switch mounts to the foregrip. Fits Peli Lights: 2320, 2330, 2390 (Cat. No. 2326). COLOUR : Black // WT.: 2.0 oz. (special orders only).

PELI RIGHT ANGLE LIGHTS

PELI LIGHT MOUNTING | HOLSTER | HOLDER STYLES

| | CAT. NO. 2407 Nylon Holster | CAT. NO. 7078 Nylon Holster | CAT. NO. 7106 | CAT. NO. 7606 | CAT. NO. 7607 | CAT. NO. 8057 Nylon Holster | | |
|--|--------------------------------|--------------------------------|---------------|---------------|----------------------------|--------------------------------|------------------------|--------------------------------|
| HOLSTER STYLES + | | | | | | | | |
| CAT NO. | | | | | | | | |
| 2300 | | | | | | | | |
| 2320 | | | | | | | | |
| 2330 | | | | | | | | |
| 2360 | | | | | | | | |
| 2370 | | | | | | | | |
| 2380 | | | | | | | | |
| 2380R | | | | | | | | |
| 2340/NVG | | | | | | | | |
| 2400/NVG | • | | | | | | | |
| 2400PL | • | | | | | | | |
| 2450 | • | | | | | | | |
| 2410 | • | | | | | | | |
| 2410PL | • | | | | | | | |
| 2460 | • | | | | | | | |
| 7000 | | | | | | | | |
| 7060 | | • | | | | | | |
| 7100 | | | • | | | | | |
| 7600 | | | | • | • | | | |
| 8040 | | | | | | • | | |
| 8050 | | | | | | • | | |
| | CAT. NO. 710 | CAT. NO. 711 | CAT. NO. 750 | CAT. NO. 770 | CAT. NO. 780 FULL HOUSE | CAT. NO. 781 ACE | CAT. NO. 782 ALL IN | CAT. NO. 783 DOUBLE DOWN |
| LIGHT AND HEADLIGHT HOLDER STYLES + | | | | | | | | |
| CAT NO. | | | | | | | | |
| 2140 | | | • | | | | | |
| 2250 | • | | • | | | | | |
| 2300 | | | • | • | | | | |
| 2320 | | | • | • | | | | |
| 2330 | | | • | • | | | | |
| 2340/NVG | | • | • | • | | | | |
| 2350 | | | | | | | | |
| 2360 | | | | | | | | |
| 2370 | | | | | | | | |
| 2380/2380R | | | | | | | | |
| 2390 | | | | • | | | | |
| 2400/2400N/NVG/PL | • | • | • | • | • | | | |
| 2410/PL | • | • | • | • | | | | |
| 2430 | • | • | • | • | | | | |
| 2450 | • | • | • | • | | | | |
| 2460 | • | • | • | • | | | | |
| 3310 | | | | • | | | | |
| 3315 | | | | • | | | | |
| 3320 | | | | • | | | | |
| 3330 | | | | • | | | | |
| 7000 | | | | | • | | | |
| All Headlamps | | | | | | | | • |

*For more information on the ATEX Zone 0 & 1 lights, see page 4-5

| CAT NO. | BATTERIES | WEIGHT W/ BATTERIES (KG) | LENGTH (CM) | ANSI LIGHT OUTPUT | ANSI RUN TIME | ANSI BEAM DISTANCE (meters) | ANSI PEAK BEAM INTENSITY (candela) | ANSI IPX RATING | CERTIFICATIONS | COLOURS | |
|--------------|---------------|---------------------------------------|--------------|-------------------|---------------|-----------------------------|------------------------------------|--------------------|----------------|---|----------------------|
| SMALL LIGHTS | 1810 | 4 LR 41 Alkaline ^A | 0.01 | 3.8 | 16 | 8h 30m | 23 | 137 | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 1900 | 2 AAA Alkaline ^A | 0.05 | 10.4 | 11 | 1h 30m | 45 | 571 | IPX7 | CI, D1/CII, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 1900Z1 | 2 AAA Alkaline ^A | 0.05 | 10.4 | 11 | 1h 30m | 45 | 571 | IPX7 | II 2 G Ex e ib IIB T4 Gb, II 2 D Ex ib IIC T100°C Db | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 1910 | 1 AAA Alkaline ^A | 0.04 | 9.7 | 72*, 14*** | 1h 45m*, 4h*** | 64*, 28*** | 1031*, 198*** | IPX7 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 1920 | 2 AAA Alkaline ^A | 0.06 | 14 | 120*, 12*** | 2h 45m*, 8h 30m*** | 87*, 27*** | 1893*, 184*** | IPX7 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 1930 | 4 LR 44 Alkaline ^A | 0.03 | 6.7 | 12 | 4h 15m | 17 | 70 | IPX4 | CI, D1/CII, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 1930Z0 | 4 LR 44 Alkaline ^A | 0.03 | 6.7 | 12 | 4h 15m | 17 | 70 | IPX4 | II 1 G Ex ia op is IIC T6/T4 Ga | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 1965Z0 | 2 AAA Alkaline ^A | 0.05 | 13.9 | 34 | 3h 45m | 45 | 512 | IPX7 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIC T90°C Da | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 2220Z1 | 2 CR2032 Lithium ^A | 0.03 | 8.9 | 9 | 34h | 12 | 38 | IPX4 | II 2 G Ex ib op is IIC T6 Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 2300 | 2 AA Alkaline ^A | 0.1 | 14.3 | 11 | 4h 30m | 43 | 478 | IPX4 | CI, D1/CII, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 2340 | 2 AA Alkaline | 0.1 | 15.9 | 10 | 4h 30m | 43 | 461 | IPX4 | CI II, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| | MEDIUM LIGHTS | 1800 | 2 C Alkaline | 0.22 | 15.2 | 21 | 7h | 131 | 4370 | IPX7 | CI II, D2 |
| 2000 | | 3 C Alkaline | 0.36 | 19.8 | 53 | 5h | 158 | 6234 | IPX7 | CI, D1/CII, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2000Z1 | | 3 C Alkaline | 0.36 | 19.8 | 39 | 6h | 177 | 7852 | IPX7 | II 2 G Ex e ib IIC T4 Gb, II 2 G Ex e ib IIC T150°C Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2010 | | 3 C Alkaline | 0.38 | 20.6 | 109 | 32h | 144 | 5189 | IPX7 | CI II III, D1 | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2010Z0 | | 3 C Alkaline | 0.38 | 20.6 | 129 | 22h | 135 | 4582 | IPX7 | II 1 G Ex ia IIC T4 T3 Ga, II 1 D Ex ia IIC T135c T200c Da IP6X | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2400 | | 4 AA Alkaline ^A | 0.2 | 16.5 | 45 | 3h 45m | 125 | 3934 | IPX7 | CI, D1/CII, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2400Z1 | | 4 AA Alkaline ^A | 0.2 | 16.5 | 38 | 4h 30m | 156 | 6194 | IPX7 | II 2 G Ex e ib IIC T4 Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2410 | | 4 AA Alkaline ^A | 0.21 | 17.8 | 183 | 5h 45m | 184 | 8480 | IPX7 | CI II III, D1 | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2410Z0 | | 4 AA Alkaline ^A | 0.21 | 17.8 | 153 | 5h 45m | 165 | 6837 | IPX7 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIC T135°C Da | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2450 | | Rechargeable NiMH ^A | 0.22 | 16.5 | 35 | 3h 30m | 122 | 3735 | IPX7 | CI II, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2460 | | Rechargeable NiMH ^A | 0.22 | 17.8 | 183 | 5h | 179 | 8050 | IPX7 | CI II, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2460Z1 | | Rechargeable NiMH ^A | 0.22 | 17.8 | 181 | 5h | 153 | 5828 | IPX7 | II 2 G Ex ib IIC T4 Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| LARGE LIGHTS | 3310PL | 3 AA Alkaline ^A | 0.18 | 15.6 | 378*, 39*** | 8h*, 202h*** | 196*, 62*** | 9580*, 961*** | IPX8 | N/A | ■ (photoluminescent) |
| | 3310ELS | 3 AA Alkaline ^A | 0.18 | 15.6 | 378*, 39*** | 8h*, 202h*** | 196*, 62*** | 9580*, 961*** | IPX8 | N/A | ■ (photoluminescent) |
| | 3315Z0 | 3 AA Alkaline ^A | 0.18 | 15.6 | 138 | 19h | 146 | 5350 | IPX7 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIC T130°C Da | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 3315RZ1 | Rechargeable Lithium-Ion ^A | 0.2 | 15.5 | 176*, 22*** | 5h 30m*, 48h*** | 127*, 44*** | 4022*, 492*** | IPX7 | II 2G Ex ib op is IIC T4 Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 3315RZ1-RA | Rechargeable Lithium-Ion | | 21 | 176*, 22*** | 5h 30m*, 48h*** | 127*, 44*** | 4022*, 492*** | IPX7 | II 2G Ex ib op is IIC T4 Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 3325Z0 | 3 AA Alkaline ^A | 0.17 | 15.4 | 155 | 16h | 140 | 4926 | IPX7 | II 1 G Ex ia IIC T4 Ga | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 9410L | Rechargeable Lithium-Ion ^A | 1.27 | 22.2 | 1203*, 553*** | 4h 30m*, 10h 30m*** | 430*, 287*** | 46,328*, 20,616*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 9415Z0 | 4 C NiMH ^A | 1.65 | 22.2 | 392*, 144*** | 4h 30m*, 11h*** | 392*, 234*** | 32767*, 13747*** | IPX4 | II 1 G Ex ia IIC T4 Ga | ■ ■ ■ ■ ■ ■ ■ ■ |

*High | **Medium | ***Low | ^ Batteries Included | Additional approvals may apply. For details go to www.peli.com

| CAT NO. | BATTERIES | WEIGHT W/ BATTERIES (KG) | LENGTH (CM) | ANSI LIGHT OUTPUT | ANSI RUN TIME | ANSI BEAM DISTANCE (meters) | ANSI PEAK BEAM INTENSITY (candela) | ANSI IPX RATING | CERTIFICATIONS | COLOURS | |
|--------------------|------------|---------------------------------------|-----------------------------|-------------------|-----------------------------|-------------------------------------|------------------------------------|--------------------------------|----------------|--|------------------------------|
| TACTICAL LIGHTS | 2350 | 1 AA Alkaline ^A | 0.1 | 10.7 | 100*, 10*** | 1h 45m*, 15h*** | 141*, 44*** | 5018*, 493*** | IPX7 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 2360 | 2 AA Alkaline ^A | 0.15 | 15.7 | 375*, 29*** | 2h 30m*, 13h*** | 192*, 53*** | 9187*, 705*** | IPX8 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 2370 | 2 AA Alkaline ^A | 0.18 | 16.3 | 106*, 13*** | 3h 45m*, 41h 15m*** | 158*, 52*** | 6283*, 684*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 2380 | 2 AA Alkaline ^A | 0.19 | 16.4 | 159*, 23*** | 3h 15m*, 13h*** | 149*, 56*** | 5579*, 779*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 2380R | Rechargeable Lithium-Ion ^A | 0.19 | 16.5 | 305*, 30*** | 3h 30m*, 25h*** | 159*, 50*** | 6317*, 613*** | IPX7 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 7000 | 2 CR123 Lithium ^A | 0.16 | 13.5 | 602*, 311** 64*** | 1h 30m*, 2h** 16h*** | 233*, 165** 75*** | 13604*, 6830** 1409*** | IPX7 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 7060 | Rechargeable Lithium-Ion ^A | 0.29 | 22 | 368*, 150** 18*** | 3h*, 9h** 45h*** | 199*, 125** 43*** | 9953*, 3922** 473*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 7100 | Lithium-Ion ^A | 0.12 | 13 | 695*, 348** 33*** | 1h 15m*, 1h 30m** 9h 15m*** | 194*, 130** 38*** | 9413*, 4247** 358*** | IPX8 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 7600 | Lithium-Ion ^A | 0.19 | 15.7 | 944*, 479** 37*** | 3h 15m*, 4h 30m** 29h*** | 225*, 157** 44*** | 12693*, 6172** 480*** | IPX8 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 8050 | Rechargeable NiMH ^A | 0.51 | 28.6 | 164 | 2h 15m | 256 | 16448 | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 8060 | Rechargeable NiMH ^A | 0.66 | 32.2 | 803*, 447** 25*** | 2h 30m*, 4h** 69h*** | 359*, 265** 62*** | 32252*, 17492** 958*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| | HEAD LAMPS | 2610Z0 | 3 AAA Alkaline ^A | 0.91 | 3.8 | 30*, 14*** | 19h*, 47h*** | 28*, 19*** | 194*, 91*** | IPX4 | II 1 G Ex ia op is IIC T4 Ga |
| 2680 | | 4 AA Alkaline ^A | 0.27 | 11.8 | 79 | 10h | 123 | 3789 | IPX7 | CI II III, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2690Z0 | | 3 AAA Alkaline ^A | 0.12 | 7.1 | 74 | 11h | 92 | 2124 | IPX7 | I M1 Ex ia I Ma, II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIC T65°C Da | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2720 | | 3 AAA Alkaline ^A | 0.11 | 6.3 | 200*, 12*** | 3h*, 103h*** | 82*, 20*** | 1684*, 103*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2740 | | 3 AAA Alkaline ^A | 0.09 | 5.7 | 66*, 36*** | 7h 15m*, 21h*** | 22*, 16*** | 122*, 68*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2745Z0 | | 3 AAA Alkaline ^A | 0.94 | 5.7 | 33*, 17*** | 20h*, 40h*** | 35*, 25*** | 309*, 155*** | IPX4 | II 1 G Ex ia IIC T4 Ga | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2750 | | 3 AAA Alkaline ^A | 0.1 | 5.7 | 259*, 71*** | 2h 30m*, 11h*** | 90*, 48*** | 2041*, 573*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2755Z0 | | 3 AAA Alkaline ^A | 0.1 | 5.7 | 72*, 34*** | 6h*, 15h*** | 57*, 40*** | 807*, 404*** | IPX4 | II 1 G Ex ia IIC T4 Ga | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2760 | | 3 AAA Alkaline ^A | 0.1 | 5.7 | 204*, 141** 95***, 42*** | 2h*, 3h 15m**, 5h** 11h*** | 111*, 80** 59***, 19*** | 3065*, 1606** 861***, 88*** | IPX4 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2765Z0 | | 3 AAA Alkaline ^A | 0.1 | 5.7 | 105*, 104** 65***, 33*** | 4h 15min*, 4h** 6h 15m***, 9h*** | 107*, 93** 63***, 9*** | 2876*, 2163** 978***, 18*** | IPX4 | II 1 G Ex ia IIC T4 Ga | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2780R | | Rechargeable Lithium-Ion ^A | 0.25 | 7.6 | 558*, 213** 95*** | 2h*, 3h** 7h 30m*** | 127*, 78** 53*** | 4060*, 1540** 695*** | IPX7 | N/A | ■ ■ ■ ■ ■ ■ ■ ■ |
| 2785Z1 | | 4 AA Alkaline ^A | 0.3 | 7.6 | Main: 215*, 106** 22*** | Main: 5h*, 13h** 98h*** | Main: 108*, 76** 34*** | 2911*, 1445** 290*** | IP54 | II 2 G Ex ib IIC T4 Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| RIGHT ANGLE LIGHTS | 2250 | 2 AA Alkaline ^A | 0.09 | 9.8 | 7 | 5h 30m | 54 | 726 | IPX4 | CI II, D2 | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 3315RZ1-RA | Rechargeable Lithium-Ion | | 21 | 176*, 22*** | 5h 30m*, 48h*** | 127*, 44*** | 4022*, 492*** | IPX7 | II 2G Ex ib op is IIC T4 Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 3610Z0 | 4 AA Alkaline | 0.3 | 19.1 | 153 | 5h 45m | 165 | 6837 | IPX7 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIC T135°C Da | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 3660Z1 | Rech. 4 AA NiMHA | 0.3 | 19.1 | 181 | 5h | 183 | 8414 | IPX7 | II 2 G Ex ib IIC T4 Gb | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 3715Z0 | 4 AA Alkaline | 0.41 | 13.6 | 189*, 90*** 23*** | 4h*, 7h*** 31h*** | 249*, 157*** 24*** | 15552*, 6150*** 150*** | IPX4 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIC T130c Da | ■ ■ ■ ■ ■ ■ ■ ■ |
| | 3765Z0 | 4 AA NiMH | 0.41 | 13.6 | 194*, 92*** 24*** | 3h 30m*, 6h 45m*** 20h 30m*** | 256*, 161** 24*** | 16392*, 6454*** 146*** | IPX4 | II 1 G Ex ia op is IIC T3 Ga | ■ ■ ■ ■ ■ ■ ■ ■ |

*High | **Medium | ***Low | ****Downcast | ^ Batteries Included | Additional approvals may apply. For details go to www.peli.com

PELI LIGHTS SPECIFICATIONS

| CAT NO. | BATTERIES | WEIGHT W/ BATTERIES (KG) | LENGTH (CM) | ANSI LIGHT OUTPUT | ANSI RUNTIME | ANSI BEAM DISTANCE (meters) | ANSI PEAK BEAM INTENSITY (candela) | ANSI IPX RATING | APPROVALS | COLOURS |
|------------|---------------------------------------|--------------------------|-------------|----------------------------|------------------------------------|-----------------------------|------------------------------------|-----------------|---|---------|
| 1900Z1 | 2 AAA Alkaline ^A | 0.05 | 10.4 | 11 | 1h 30m | 45 | 571 | IPX7 | II 2 G Ex e ib IIB T4 Gb, II 2 D Ex ib IIIC T100°C Db | ■ □ |
| 1930Z0 | 4 LR 44 Alkaline ^A | 0.03 | 6.7 | 12 | 4h 15m | 17 | 70 | IPX4 | II 1 G Ex ia op is IIC T6/T4 Ga | □ |
| 1965Z0 | 2 AAA Alkaline ^A | 0.05 | 13.9 | 34 | 3h 45m | 45 | 512 | IPX7 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T90°C Da | ■ □ |
| 2000Z1 | 3 C Alkaline | 0.36 | 19.8 | 39 | 6h | 177 | 7852 | IPX7 | II 2 G Ex e ib IIC T4 Gb, II 2 G Ex e ib IIC T150°C Gb | ■ □ |
| 2010Z0 | 3 C Alkaline | 0.38 | 20.6 | 129 | 22h | 135 | 4582 | IPX7 | II 1 G Ex ia IIC T4 T3 Ga, II 1 D ia IIIC T135c T200c Da IP6X | ■ |
| 2220Z1 | 2 CR2032 Lithium ^A | 0.03 | 8.9 | 9 | 34h | 12 | 38 | IPX4 | II 2 G Ex ib op is IIC T6 Gb | ■ □ |
| 2400Z1 | 4 AA Alkaline ^A | 0.2 | 16.5 | 38 | 4h 30m | 156 | 6194 | IPX7 | II 2 G Ex e ib IIC T4 Gb | ■ □ |
| 2410Z0 | 4 AA Alkaline ^A | 0.21 | 17.8 | 153 | 5h 45m | 165 | 6837 | IPX7 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T135°C Da | ■ □ |
| 2460Z1 | Rechargeable NiMH ^A | 0.22 | 17.8 | 112 | 4h 30m | 153 | 5828 | IPX7 | II 2 G Ex ib IIC T4 Gb | ■ |
| 2610Z0 | 3 AAA Alkaline ^A | 0.91 | 3.8 | 30*, 14*** | 19h*, 47h*** | 28*, 19*** | 194*, 91*** | IPX4 | II 1 G Ex ia op is IIC T4 Ga | ■ |
| 2690Z0 | 3 AAA Alkaline ^A | 0.12 | 7.1 | 74 | 11h | 92 | 2124 | IPX7 | I M1 Ex ia I Ma, II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T65°C Da | ■ |
| 2745Z0 | 3 AAA Alkaline ^A | 0.94 | 5.7 | 33*, 17*** | 20h*, 40h*** | 35*, 25*** | 309*, 155*** | IPX4 | II 1 G Ex ia IIC T4 Ga | ■ □ |
| 2755Z0 | 3 AAA Alkaline ^A | 0.1 | 5.7 | 72*, 34*** | 6h*, 15h*** | 57*, 40*** | 807*, 404*** | IPX4 | II 1 G Ex ia IIC T4 Ga | ■ □ |
| 2765Z0 | 3 AAA Alkaline ^A | 0.1 | 5.7 | 105*, 104**, 65***, 33**** | 4h 15min*, 4h**, 6h 15m***, 9h**** | 107*, 93**, 63***, 9**** | 2876*, 2163**, 978***, 18**** | IPX4 | II 1 G Ex ia IIC T4 Ga | ■ □ |
| 2785Z1 | 4 AA Alkaline ^A | 0.3 | 7.6 | Main: 215*, 106**, 22*** | Main: 5h*, 13h**, 98h*** | Main: 108*, 76**, 34*** | Main: 2911*, 1445**, 290*** | IP54 | II 2 G Ex ib IIC T4 Gb | ■ □ |
| 3315Z0 | 3 AA Alkaline ^A | 0.18 | 15.6 | 138 | 19h | 146 | 5350 | IPX7 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T130°C Da | ■ |
| 3315RZ1 | Rechargeable Lithium-Ion ^A | 0.2 | 15.5 | 176*, 22*** | 5h 30m*, 48h*** | 127*, 44*** | 4022*, 492*** | IPX7 | II 2G Ex ib op is IIC T4 Gb | ■ |
| 3315RZ1-RA | Rechargeable Lithium-Ion | | 21 | 176*, 22*** | 5h 30m*, 48h*** | 127*, 44*** | 4022*, 492*** | IPX7 | II 2G Ex ib op is IIC T4 Gb | ■ |
| 3325Z0 | 3 AA Alkaline ^A | 0.17 | 15.4 | 155 | 16h | 140 | 4926 | IPX7 | II 1 G Ex ia IIC T4 Ga | ■ |
| 3610Z0 | 4 AA Alkaline | 0.3 | 19.1 | 153 | 5h 45m | 165 | 6837 | IPX7 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T135°C Da | ■ |
| 3660Z1 | Rech. 4 AA NiMHA | 0.3 | 19.1 | 176 | 3h 45m | 183 | 8414 | IPX7 | II 2 G Ex ib IIC T4 Gb | ■ |
| 3715Z0 | 4 AA Alkaline | 0.41 | 13.6 | 189*, 90***, 23**** | 4h*, 7h***, 31h**** | 249*, 157***, 24**** | 15552*, 6150***, 150**** | IPX4 | II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T130c Da | ■ |
| 3765Z0 | 4 AA NiMH | 0.41 | 13.6 | 194*, 92***, 24**** | 3h 30m*, 6h 45m***, 20h 30m**** | 256*, 161***, 24**** | 16392*, 6454***, 146**** | IPX4 | II 1 G Ex ia op is IIC T3 Ga | ■ |
| 9415Z0 | 4 C NiMH ^A | 1.65 | 22.2 | 392*, 144*** | 4h 30m*, 11h*** | 392*, 234*** | 32767*, 13747*** | IPX4 | II 1 G Ex ia IIC T4 Ga | ■ |

*High | **Medium | ***Low | ****Downcast | ^ Batteries Included | Additional approvals may apply. For details go to www.peli.com

SEE SPECIFICATIONS CHART FOR ADDITIONAL LIGHT PERFORMANCE DATA | PERFORMANCE DATA IS TO FL 1 STANDARDS (APPLIES TO TORCHES ONLY). All details included in this catalogue are correct when printed but for most updated information please visit www.peli.com and www.pelicatalogue.com

CUSTOM LABELS

Peli Products offers the ultimate in private labeling. You can put your company name and logo or a special statement on many Peli lights. Our in-house private label molding and production department has complete short and long run capabilities for a variety of custom applications and custom colours. We have the latest hot stamping equipment, utilizing the world's most durable inks and foils in our screening, hot tipping, embossing, and moulding programs.



GRAPHIC DESIGN STUDIO

Our in-house graphics studio will take your logo and size it appropriately to the torch of your choice.



HOT STAMPING

Our hot stamping department, equipped with the latest technology in custom imprinting. Minimum quantities apply



100% ACCURACY

Peli's strict QA inspection team will check for quality of print and 100% accuracy in colour and placement.



PELI CUSTOM LABELS | LIGHTING FEATURES

PELI LIGHTING TOOLS: MORE THAN A TORCH.

Here are just a few features that make our lighting tools shine:



LEGENDARY LIFETIME GUARANTEE



SELF PROGRAMMABLE
(Selected models only)



GESTURE ACTIVATION
(On selected models only)



USB RECHARGEABLE
(On selected models only)



PHOTOLUMINESCENT DESIGNS
(Selected models only)



PIVOTING 60° HEAD
(On selected models only)




DOWNCAST LIGHTING FEATURES
(On selected models only)

SEE SPECIFICATIONS CHART FOR ADDITIONAL LIGHT PERFORMANCE DATA | PERFORMANCE DATA IS TO FL 1 STANDARDS (APPLIES TO TORCHES ONLY). All details included in this catalogue are correct when printed but for most updated information please visit www.peli.com and www.pelicatalogue.com

SMALL LIGHTS PGS 06-07



MEDIUM LIGHTS PGS 08 - 10



MEDIUM LIGHTS PGS 08 - 10



LARGE LIGHTS PGS 11




ATEX LIGHTS ZONE 0 & 1 (CAT. 1 & 2) PGS 12 - 15



ATEX LIGHTS ZONE 0 & 1 (CAT. 1 & 2) PGS 12 - 15



ATEX LIGHTS ZONE 0 & 1 (CAT. 1 & 2) PGS 12 - 15



TACTICAL LIGHTS PGS 16 - 17



TACTICAL LIGHTS PGS 16 - 17



HEADLAMPS PGS 18 - 19



HEADLAMPS PGS 18 - 19



RIGHT ANGLE LIGHTS PGS 20

