


SD5500



Compressed air meter

SDR14DGXFRKG/US-100



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	0.8...250 l/min	0.3...82.9 m/s	0.05...15 m³/h
Process connection	threaded connection G 1/4 DN8		

Application

Application	for industrial applications
Media	compressed air
Medium temperature [°C]	-10...60
Min. bursting pressure [bar]	64
Pressure rating [bar]	16

Electrical data

Operating voltage [V]	18...30 DC; (according to EN 50178 SELV/PELV)
Current consumption [mA]	< 80
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	1

SD5500



Compressed air meter

SDR14DGXFRKG/US-100

Inputs / outputs			
Inputs		Outputs	
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1	
Inputs			
Inputs			counter reset
Outputs			
Output signal		switching signal; analogue signal; pulse signal; IO-Link; (configurable)	
Electrical design		PNP/NPN	
Number of digital outputs		2	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2.5	
Permanent current rating of switching output DC	[mA]	150; (per output)	
Number of analogue outputs		1	
Analogue current output	[mA]	4...20; (scalable)	
Max. load	[Ω]	500	
Pulse output		consumed quantity meter	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range		0.8...250 l/min	0.05...15 m³/h
Display range		0...300 l/min	0...18 m³/h
Resolution		0.2 l/min	0.01 m³/h
Set point SP		2.2...249.9 l/min	0.13...14.99 m³/h
Reset point rP		0.9...248.7 l/min	0.06...14.92 m³/h
Analogue start point ASP		0...200 l/min	0...12 m³/h
Analogue end point AEP		50...250 l/min	3...15 m³/h
Low flow cut-off LFC		0.3...2.7 l/min	0.02...0.16 m³/h
In steps of		0.1 l/min	0.01 m³/h
Pressure monitoring			
Measuring range		[bar]	-1...16
Display range		[bar]	-1...20
Resolution		[bar]	0.05
Set point SP		[bar]	-0.92...16
Reset point rP		[bar]	-1...15.92
Analogue start point		[bar]	-1...12.8
Analogue end point		[bar]	2.2...16
In steps of		[bar]	0.01

SD5500



Compressed air meter

SDR14DGXFRKG/US-100

Volumetric flow quantity monitoring		
Measuring range		0...100000000 m ³
Display range		0...100000000 m ³
Set point SP		0.001...10000000 m ³
Pulse value		0.001...1000000 m ³
In steps of		0.0001 m ³
Pulse length	[s]	0.01...2
Temperature monitoring		
Measuring range		-10...60 °C
Display range		-24...74 °C
Resolution		0.2 °C
Set point SP		-9.7...60 °C
Reset point rP		-10...59.7 °C
Analogue start point		-10...46 °C
Analogue end point		4...60 °C
In steps of		0.1 °C
Accuracy / deviations		
Temperature coefficient	[1/K]	± 0,07 % MW
Accuracy (in the measuring range)		class 141: ± (2 % MW + 0,5 % MEW); class 344: ± (6 % MW + 0,6 % MEW) ; air quality to ISO 8573-1:2010; at medium temperature 23 °C
Repeatability		0,8 % MW + 0,2 % MEW
Pressure monitoring		
Repeatability	[% of the final value]	± 0,2
Characteristics deviation	[% of the final value]	< ± 0,5; (BFSL = Best Fit Straight Line)
Greatest TEMPCO of the span	[% MEW / 10 K]	± 0,15
Greatest TEMPCO of the zero point	[% MEW / 10 K]	± 0,25
Temperature monitoring		
Accuracy	[K]	± 0,5; (medium flow in the limit area of the flow measurement range)
Response times		
Response time	[s]	0.1; (dAP = 0)
Damping for the switching output dAP	[s]	0...5
Pressure monitoring		
Response time	[s]	0.05
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 0,5
Software / programming		
Parameter setting options		hysteresis / window; normally open / normally closed; current/pulse output; display can be rotated and switched off; Display unit; totaliser

SD5500



Compressed air meter

SDR14DGXFRKG/US-100

Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9 CDV
IO-Link device ID		860 d / 00 03 5c h
Profiles		Digital Measuring Sensor (0x800A), Identification and Diagnosis (0x4000)
SIO mode		yes
Required master port type		A
Process data analogue		8
Process data binary		2
Min. process cycle time	[ms]	7.2
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...85
Max. relative air humidity	[%]	90
Protection		IP 65; IP 67
Tests / approvals		
EMC		DIN EN 60947-5-9
Vibration resistance		DIN EN 68000-2-6
MTTF	[years]	183
UL approval		UL Approval no. I012 File number UL E174189
Pressure Equipment Directive		Sound engineering practice; can be used for stable gases fluid group 2
Mechanical data		
Weight	[g]	556
Materials		PBT+PC-GF30; PPS GF40; stainless steel (1.4301 / 304); stainless steel (1.4305 / 303); steel (1.5523) galvanised; 2.0401 (brass / CW614N); FKM
Materials (wetted parts)		EN AW-6082 (aluminium); stainless steel (1.4305 / 303); FKM; ceramics glass passivated; PPS GF40; Al2O3 (ceramics); acrylate
Process connection		threaded connection G 1/4 DN8
Displays / operating elements		
Display		colour display 1,44", 128 x 128 pixels 2 x LED, yellow
Remarks		
Remarks		MW = measured value
		MEW = Final value of the measuring range
		Measuring, display and setting ranges refer to the standard volume flow according to DIN ISO 2533.
		For information about installation and operation please see the operating instructions.
Pack quantity		1 pcs.
Electrical connection		
Connector:	1 x M12	

SD5500




Compressed air meter

SDR14DGXFRKG/US-100



Connection



- OUT1/IO-Link:
- switching output flow
 - switching output temperature
 - switching output pressure
 - Pulse output quantity meter
 - signal output Preset counter
- OUT2/InD:
- switching output flow
 - switching output temperature
 - switching output pressure
 - analogue output flow
 - analogue output temperature
 - analogue output pressure
 - signal output Preset counter
 - Pulse output quantity meter
 - input counter reset