

## MIRO 6.2 TIMER ON-DELAY

IN: 24 VDC - OUT: 250 VAC/DC / 6A



Relay output




Switch on delay: 3...300 s

Screw terminals

### [Link to Product](#)


#### Illustration





Product may differ from Image

### Approvals



### Utilization category

AC-12	6 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)
DC-13	1 A (24 V DC); 0.2 A (110 V DC); 0.1 A (230 V DC)

### Input

Input voltage	24 V DC (+10 -15 %) input A
Input current	20 mA (input A)

Control voltage	24 V DC (+10 -15 %) input B
-----------------	-----------------------------

Control current	5 mA (input B)
-----------------	----------------

#### General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
--------------------	--

Test isolation voltage	4 kV; safe separation (EN 60947-1)
------------------------	------------------------------------

Mounting method	DIN-rail mountable (EN 60715)
-----------------	-------------------------------

Temperature range	0...+55 °C
-------------------	------------

Dimensions H × W × D	90×6.2×65 mm
----------------------	--------------

#### Output

Output voltage	max. 250 V AC/DC
----------------	------------------

Output current	max. 6 A
----------------	----------

Min. load current	100 mA (12 V DC)
-------------------	------------------

Output rating	max. 1500 VA/120 W
---------------	--------------------

Switching frequency	max. 10 Hz
---------------------	------------

Contact material	Ag Sn O <sub>2</sub>
------------------	----------------------

Energize/release/contact bounce time	10/15/1.5 ms
--------------------------------------	--------------

#### Commercial data

country of origin	CZ
-------------------	----

customs tariff number	85364900
-----------------------	----------

minimum order quantity	1
------------------------	---