DATA SHEET

TH01 HANDLE FOR PLUG MOUNTED PROBES TYPE 'T'

HANDLE FOR PLUG MOUNTED PROBES - Type 'T'

Description

This handle is used in conjunction with the range of plug mounted probes offered by TME. The socket in the end of the handle allows for the plug mounted probes to be inserted into the handle. This means that a variety of temperature measurements may be performed using the socket in the handle and different plug mounted probes.

Construction

Handle which includes miniature thermocouple socket into which any one of the TME plug mounted probes may be inserted. Complete with 2M curly polyurethane cable with moulded connector. Complete waterproof assembly.

Sensor Features

TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.

This results in a solid handle as opposed to a hollow handle. This is particularly important as there is often damage to the handles caused by excess heat. With a hollow handle it is possible to puncture the outer plastic and damage the sensor irreparably.

WATERPROOF HANDLE

Due to the total encapsulation method used, all TME probe handles are completely waterproof.

> TOUGH POLYURETHANE CABLE

- Polyurethane cables are used in place of the standard PVC for the following reasons:-
- Greater retractability
- · Enhanced memory of it's curl
- Non-Toxic
- Greater mechanical strength for durability
- 12 X 0.2mm wires used internally for greater strength.
- PTFE inner insulation for strength and retractability.

HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT

Type 'T' Thermocouple : ½ Class I (±0.25°C ±0.15%)

POLYPROPYLENE HANDLES

Polypropylene is an extremely tough and durable material, commonly used for milk crates, it has good low temperature performance and a relatively high melt temperature. It performs exceptionally well under chemical attack.

➤ WIDE AMBIENT TEMPERATURE SPECIFICATION : -50 TO 50 °C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

DESCRIPTION	APPLICATION
SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT
MAX / MIN HOLD INSTRUMENT	HIGH ACCURACY INSTRUMENT WITH MAX, MIN AND HOLD FEATURES
DIFFERENTIAL INSTRUMENT	DUAL INPUT INSTRUMENT FOR DIFFERENTIAL MEASUREMENTS
THERMOCOUPLE SIMULATOR	HIGH ACCURACY SIMULATOR WITH MEASUREMENT FACILITY
	SINGLE INPUT INSTRUMENT MAX / MIN HOLD INSTRUMENT DIFFERENTIAL INSTRUMENT