



PLUG-IN RELAY COMPACT UNIT 230V AC, 2 CO LED  
MODULE RED SOCKET W. LOGIC ISOLATION PLUG-  
IN TERMINAL (PUSH-IN)

Figure similar

### General technical data:

Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
<b>Type of voltage</b>		AC
<b>Control supply voltage</b>		
• with AC		
— at 50 Hz Rated value		
— minimum	V	230
— maximum	V	230
— at 60 Hz Rated value		
— minimum	V	230
— maximum	V	230
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		4
Operating current of the auxiliary contacts		
• at DC-13		
— at 24 V	A	8
• at AC-15		
— at 230 V	A	5
<b>Design of the switching function positively driven</b>		No
<b>Switching behavior</b>		monostable

#### Mechanical data:

Type of electrical connection		spring-loaded terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		Yes
Width	mm	28
Height	mm	79
Depth	mm	98

#### Certificates/ approvals:

General Product Approval

other

[Declaration of Conformity](#)



#### Further information

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZS:PT2D5T30>

##### Information- and Downloadcenter (Catalogs, Brochures,...)


<http://www.siemens.com/industrial-controls/catalogs>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:PT2D5T30>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=LZS:PT2D5T30&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZS:PT2D5T30&lang=en)



W9 4444; LZS:PT2D5L24\_ALL

last modified:

15.01.2015