

DICHT-BECHERBLINDNIETE



FLACHRUNDKOPF MIT GERILLTEM NIETDORN (~ DIN EN ISO 16585)

SEALED BLIND RIVETS

DOMED HEAD WITH GROOVED MANDREL (~ DIN EN ISO 16585)

RIVETS ÉTANCHES


TÊTE PLATE AVEC CLOU CANNÉLÉ (~ DIN EN ISO 16585)










Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]


Edelstahl C1 [1.4021]
Stainless steel C1 [AISI 420]
Acier inox C1 [1.4021]








Ø 3,2 mm

D1 = 3,2 + 0,08 / - 0,10 mm
D2 = 6,0 + / - 0,24 mm
k = 0,9 + / - 0,3 mm
d = 1,9 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,3 mm


						
3,2 x 6,0 mm	0,5 - 1,5 mm	21801 32600	2000 N	2500 N	1000	10000
3,2 x 8,0 mm	1,5 - 3,0 mm	21801 32800			1000	10000
3,2 x 9,5 mm	3,0 - 5,0 mm	21801 32950			1000	10000
3,2 x 12,0 mm	5,0 - 7,0 mm	21801 32120			1000	10000
3,2 x 14,0 mm	7,0 - 9,0 mm	21801 32140			1000	10000
3,2 x 16,0 mm	9,0 - 11,0 mm	21801 32160			1000	10000








Ø 4,0 mm

D1 = 4,0 + 0,08 / - 0,10 mm
D2 = 8,0 + / - 0,29 mm
k = 1,3 + / - 0,3 mm
d = 2,3 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,1 mm


						
4,0 x 6,0 mm	0,5 - 1,5 mm	21801 40600	3000 N	4000 N	500	5000
4,0 x 8,0 mm	1,5 - 3,0 mm	21801 40800			500	5000
4,0 x 9,5 mm	3,0 - 5,0 mm	21801 40950			500	5000
4,0 x 12,0 mm	5,0 - 6,5 mm	21801 40120			500	5000
4,0 x 16,0 mm	6,5 - 10,5 mm	21801 40160			500	5000








Ø 4,8 mm

D1 = 4,8 + 0,08 / - 0,10 mm
D2 = 9,5 + / - 0,29 mm
k = 1,6 + / - 0,3 mm
d = 2,9 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,9 mm

						
4,8 x 8,0 mm	1,0 - 3,0 mm	21801 48800	4500 N	5500 N	250	2500
4,8 x 9,5 mm	3,0 - 5,0 mm	21801 48950			250	2500
4,8 x 12,0 mm	5,0 - 6,5 mm	21801 48120			250	2500
4,8 x 16,0 mm	6,5 - 10,5 mm	21801 48160			250	2500
4,8 x 20,0 mm	10,5 - 14,0 mm	21801 48200			250	2500

Ø 6,4 mm

D1 = 6,4 + 0,08 / - 0,15 mm
D2 = 12,7 + / - 0,35 mm
k = 2,1 + / - 0,3 mm
d = 3,9 mm
P ≥ 31,0 mm
L = + 1,0 / - 0,2 mm
 6,5 mm

						
6,4 x 14,2 mm	1,5 - 5,0 mm	21801 64142	6800 N	8700 N	250	2500
6,4 x 15,5 mm	5,0 - 7,9 mm	21801 64155			250	2500
6,4 x 20,0 mm	7,9 - 12,8 mm	21801 64200			250	2500