



HP w1907v 19" Wide Flat Panel Monitor



- **Get a Wider and Brighter View**

Enjoy a brilliant and immersive widescreen viewing experience, thanks to this impressive 19-inch wide flat-panel monitor with HP BrightView Technology which makes colours richer and pictures sharper

- **Outstanding Picture Quality**

Experience uncompromised widescreen viewing performance for video, photos, games and more, thanks to easy to use Quick View modes, fast 5 ms response time, 1440 x 900 optimal resolution, and 1000:1 contrast for photo-realistic quality

- **Stylish Design and Easy Clip**

A leading style, and improved ergonomics make it easy to adjust the monitor to work or play comfortably. You can also save space and personalize your monitor with Easy Clip by clipping on photo holders, cameras, or accessories

- **My Display software for greater performance**

My Display software will provide you with easy and convenient one touch adjustment of your HP display performance. Easy to set up and use, you simply plug and play the monitor to get started

HP w1907v 19" Wide Flat Panel Monitor

Specifications	Display Size: 19" (48.3 cm) diagonal and viewable image - 41.0 cm x 25.6 cm (WxH) Display type: Wide Thin Film Transistor Liquid Crystal Display active matrix Surface treatment: HP BrightView Technology Pixel pitch: 0.285 mm Refresh response time: 5ms (rise + fall) Brightness: 300 cd/m2 (typical) Contrast ratio: 1000:1 (typical) Viewing angle: 160 degrees horizontal and 160 degrees vertical viewing angle (10:1 minimum contrast ratio) Display, Maximum Pixel Rate: 136.7 MHz in 1440x900 at 60Hz	Mechanical specifications	Dimensions (W x D x H): 462 x 380 x 184 mm Weight: 5.0 kg Package Dimensions (W x D x H): 489 x 536 x 163 mm Package Weight: 6.8 kg Operating Temperature Range: 0° C to 40° C, 15%-90% relative humidity non-condensing Storage Temperature Range: - 20° C to 60° C, 15%-90% relative humidity
Interface specifications	Video input signal: Analog (15-pin miniature D-sub VGA) Display resolution: 1440 x 900 @ 60Hz max Recommended resolution: 1440 x 900 @ 60Hz (native recommended) plus all VESA modes up to 1440 x 900 @ 60Hz Colour: Support true colour, up to 16 Million colours (16.2M) Scan rates: 55-75Hz vertical, 30-83kHz horizontal	Regulatory	Compliance Industry Standards: CE Marking, 9241-3,7,8 VDT guidelines, ISO 13406-2 pixel defect guidelines, MPR-II, FCC approval, Microsoft Windows certified (Microsoft Windows 2000, Microsoft Windows XP, and Microsoft Vista), UL listed, GOST (Russia), SASO (Saudi Arabia), SABS (South Africa), SEMKO
Features	Multimedia: Integrated active speakers (2 x 2W /channel) with front volume control Physical security features: Kensington lock ready Display moving angle: Swivel and vertical tilt range -5 degrees to 25 degrees; standard 4 hole pattern 100mm x 100mm screw wall-mounting option Plug and play: Yes	Additional information	Warranty: Limited one-year part and repair labour warranty (certain restrictions and exclusions apply) Box Content: Monitor, AC power cord (1.9 m), VGA video cable (1.8 m), audio cable, documentation CD, and Limited Warranty Card Ordering info: GB205AA#ABB (Europe), UPC 883585029839 GB205AA#B14 (Belgium), UPC 883585029877 GB205AA#ABU (UK & Ireland), UPC 883585029846 GB205AA#AR8 (Switzerland), UPC 883585029853 GB205AA#ABY (Denmark), UPC 883585029860 GD868AA#ABV (Middle East), UPC 883585080441
Power	Power Supply and Power Requirements: External AC 100-240V, auto-ranging, 50-60Hz Power Consumption: 49 watts maximum on operating mode; 2 watts max in power saving mode		
User controls	Display User Control Options: Brightness, Contrast, Image Control, Color, Quick View, Language, Management, Information, Factory Reset, Exit, 8 Languages		

© 2007 Hewlett-Packard Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower. 02/07

