

## Product information

# 79 32 125 ESD

## Precision Electronics Side Cutter ESD

DIN ISO 9654 DIN EN 61 340-5



- Electrically discharging handles - dissipative
- Pointed head
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Precision cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened




### General

Article No.	79 32 125 ESD
EAN	4003773061557
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	61 g
Dimensions	125 x 61 x 19 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.1 mm
Cutting capacities hard wire (diameter)	Ø 0.6 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 1.5 mm
Jaw length (B)	11 mm
Jaw thickness (joint) (D)	6.5 mm
Head width (A)	11 mm
ESD	yes

## Technical details



*technical change and errors excepted*

