


# DIN 41612



## Type G Female Connector



**Type:** Female connector straight with 4 rows

**Termination:** Press-fit, solder

**Number of contacts:** 64

**Pitch:** 5.08 mm x 3.81 mm


**Operational current:** 5.6 A

**Packaging:** Box

**Standard:** IEC 60603-2



Technical Specifications on page 36



### Accessories

- Processing tools p. 300
- Coding p. 132

### Mating connector / Application:

 Type G Male connector (p. 100)



**Press-fit - Performance level II** •••

No. of contacts	Contact arrangement	Termination length L	
		6.0 mm	22 mm
		Part number	
64		112-60064	112-60065

**On request**

- performance level I + III or customized
- special contact length
- without flange
- contact arrangement



**Solder - Performance level II** •••

No. of contacts	Contact arrangement	Termination length L			
		4.5 mm Ø 1 mm	22 mm	4.5 mm Ø 0.7 mm	5.5 / 10.9 mm <small>Manual soldering with solder lug</small>
		Part number			
64		112-40064	112-40065	112-40084	112-40066

**On request**

- performance level I + III or customized
- special contact length
- also in THTR
- Board-Lock p. 131
- contact arrangement