

# UNIVERSAL ENCLOSURES

UNIVERSAL ENCLOSURES

## 1100 Series Stylish ABS Cases

### 1101 ABS Lid

Aesthetic electronic enclosures with solid ABS lids, designed for a broad range of applications.

- Lid and base moulded in ABS- UL94-V0
- Lid mounted by four M3 machine screws
- Bevelled edges and curved side walls
- 1.2mm membrane keypad recesses in lid and base
- Polished finish for ease of cleaning and stylish appearance
- Deep profile for maximum internal volume
- Plastic standoffs in base for mounting of PCBs
- Excellent properties for machining



#### SPECIFICATION

Materials Lid & base high impact ABS-UL94-V0


Operating temperature Resistant to temperatures up to 85°C

Protection class IP54

Standard colours Light grey similar to RAL 7035

Standard unit includes: Base & Lid  
4 x M3 machine screws

LIGHT GREY	LENGTH	WIDTH	HEIGHT
CSACST001	90mm	50mm	35mm
CSACST002	110mm	60mm	40mm
CSACST003	125mm	75mm	50mm
CSACST004	155mm	95mm	60mm
CSACST005	190mm	115mm	75mm
CSACST006	220mm	140mm	90mm



### 1102 Transparent Lid

Electronic enclosures featuring a transparent lid, designed for applications that require visible electronics. High impact polycarbonate smoked effect lid.

- Box moulded in ABS, UL94-V0
- Lid moulded in transparent, Polycarbonate, UL94-V0
- Lid mounted by four M3 machines screws
- Bevelled edges and curved side walls
- 1.2mm membrane keypad recesses in lid and base
- Polished finish for ease of cleaning and stylish appearance
- Deep profile for maximum internal volume
- Pillars in base for mounting of PCBs
- Excellent properties for machining



#### SPECIFICATION

Materials Lid high impact PC, UL94-V0  
Base high impact ABS, UL94-V0

Operating temperature Base resistant to temperatures up to 85°C  
Lid resistant to temperatures up to 120°C

Protection class IP54

Standard colours Light grey similar to RAL 7035

Standard unit includes: Base & lid  
4 x M3 machine screws

LIGHT GREY	LENGTH	WIDTH	HEIGHT
CSACTT001	90mm	50mm	35mm
CSACTT002	110mm	60mm	40mm
CSACTT003	125mm	75mm	50mm
CSACTT004	155mm	95mm	60mm
CSACTT005	190mm	115mm	75mm
CSACTT006	220mm	140mm	90mm

