Wiha SoftFinish[®].

The convenient expert for dry applications.



The Wiha SoftFinish® zone features a solid moulded core with soft outer grip. This requires less force, yet achieves 40% more torque than conventional handles. The handle is shaped to fit comfortably in the hand, providing maximum through forces in dry working conditions.

If a stuck screw has to be loosened, a precise hammer blow can be applied to the solid steel cap. Due to the hex blade extending through the handle to the steel cap, there is no loss of impact energy.







The solid steel cap at the end of the SoftFinish® handle enables controlled hammer blows, for example, when loosening a tight screw.

Due to the solid steel cap and hex blade extending through the handle, there is no loss of impact energy when a precise hammer blow is applied.

Blade with hex bolster for wrenches to use on particularly tight screws.

Wiha SoftFinish®.

- Multi-component SoftFinish[®] handle provides maximum user comfort
- Ergonomically perfect handle design
- Printed screw symbol on handle end for fast identification
- Available in versions with round blade, hex blade or hex blade with solid steel cap
- Blade made of high quality CVM-steel, through-hardened and chrome plated
- Wiha ChromTop®-finish on tip for a perfect fit every time



Wiha SoftFinish[®].

The convenient expert for dry applications.

For TORX[®] and TORX[®] tamper resistant screws.

۲	Nogeles	- And				wiha 💿
362R)® screwc crews in	
Blade:	High qua chrome-	ality chron plated.	ne-vana	dium-mo	olybdenur	n steel, through hardened, it every time.
Handle:						ent handle with roll-off pro-
Application:	For settir	ng and tig	htening	TORX®	screws in	difficult to access areas.
Order-No.	۲			_ _		—
27736	Т6	60	3.5	164	23	10
27737	T7	60	3.5	164	23	10
27738	Т8	60	3.5	164	23	10
27739	Т9	60	4.0	171	30	10
27740	T10	80	4.0	191	30	10
27741	T15	80	4.0	191	30	10

For TORX PLUS® screws.

20IP

25IP

27IP

30IP

40IP

4.0

4.5

5.5

6.0

7.0



torque than the TORX® profile.								
۲				-	-			
6IP	60	3.5	164	23	10			
7IP	60	3.5	164	23	10			
8IP	60	3.5	164	23	10			
9IP	60	4.0	171	30	10			
10IP	80	4.0	191	30	10			
15IP	80	4.0	191	30	10			

100	wiha 🐠

T20

T25

T27

T30

T40

4.0

4.5

5.5

6.0

7.0

362TR Blade: Handle:	SoftFinish® TORX® Tamper Resistant screwdriver. With borehole in the blade tip. For TORX® screws with locking pin. High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time. With borehole in the blade tip. Ergonomic Wiha SoftFinish® multi-component handle with roll-off pro-						
	tection.						
Order-No.	۲	——	•	_ _	<u>+</u>	—	
03106	T7H	60	3.5	164	23	10	
03107	T8H	60	3.5	164	23	10	
03108	T9H	60	4.0	171	30	10	
26456	T9H	300	4.0	411	30	5	
01300	T10H	80	4.0	191	30	10	
26457	T10H	300	4.0	411	30	5	
01301	T15H	80	4.0	191	30	10	
26458	T15H	300	5.0	411	30	5	
01302	T20H	100	4.0	211	30	10	
28005	T20H	300	5.0	411	30	5	
01303	T25H	100	4.5	211	30	10	
01304	T27H	115	5.5	233	36	10	
01305	T30H	115	6.0	233	36	10	
01306	T40H	130	7.0	254	41	10	



	Hagic	spine							
362RIP	SoftFinish® TORX PLUS® MagicSpring® screwdriver.								
	Retaining spring holds TORX PLUS [®] screws in place.								
Blade:	High quality chrome-vanadium-molybdenum steel, through hardened,								
	chrome-plated.								
	Wiha ChromTop [®] finish on tip for a perfect fit every time.								
Handle:	Ergonomic Wiha SoftFinish® multi-component handle with roll-off pro-								
	tection.								
Application:	For setting and tightening TORX PLUS® screws in hard to reach areas.								
Extra:	The stronger profile of the TORX PLUS® tip allows up to 25% extra								
	torque than the TORX [®] profile.								
	-								
Order-No.	۲					-			
28760	6IP	60	3.5	164	23	10			
28761	7IP	60	3.5	164	23	10			
28762	8IP	60	3.5	164	23	10			
28763	9IP	60	4.0	171	30	10			
28764	10IP	80	4.0	191	30	10			
28765	15IP	80	4.0	191	30	10			
28766	20IP	100	4.0	218	36	10			
28767	25IP	100	4.5	218	36	10			
28768	27IP	115	5.5	233	36	10			

30IP

40IP

6.0

7.0