

SVUC boring bar steel positive, left-hand

For longitudinal and copy turning with VC indexable insert

ATORN[®]

Application

For longitudinal and copy turning with VC indexable insert 35°.

Version

- Precision-made boring bar, **steel**, with internal cooling, type V, attack angle 93°, tip angle 35°, clearance angle 7°

Advantage

- Very narrow geometry optimised for contour-turning work
- Positive body geometry ensures low cutting forces



Art. No.	17849 027
ISO name	A 20 R SVUC R/L 11
Min. bore diameter	25 mm
Shaft diameter	20 mm
Cutting edge height	9 mm
Clearance length	20.5 mm
Length	200 mm
Clamping surface height	18 mm
Programming size	13 mm
Suitable for indexable inserts	VC.. 1103..
Tool design	Left

EAN-Code

4050293540147