

RAGE 4

UK 110v: 081-0007, UK 230v: 081-0006, EU 230v: 081-0008

185MM TCT MULTI-MATERIAL CHOP SAW

- Multi-Material Cutting Technology
- 1250W Powerful Hi-Torque Motor
- 97mm x 46mm Rectangle at 90°
- 45mm Square at 90°
- 46mmØ Round Tube Capacity
- 0°- 45° Mitre Cutting Capability
- Fast & Easy Blade Change
- 3 Year Limited Warranty

185MM BLADES	BORE	KERF	TEETH/RIM	
Multi-Material TCT	20mm	1.7mm	20	R185TCT-20CS
Diamond Blade	20mm	2.3mm	Segmented	RAGEBLADE185DIAMOND

8.95 kg
19.7 lbs



DISC CUTTER

UK 110v: 008-0002, UK 230v: 008-0001, EU 230v: 008-0004

305MM ELECTRIC CONCRETE SAW

- Cuts Reinforced Concrete, Stone & Brick
- 2400W Powerful Hi-Torque Motor
- Electric Powered
- 100mm Depth of Cut
- Electric Motor = No Petrol Fumes
- Diamond Blade Included
- 2 Years Limited Warranty

305MM BLADE	BORE	KERF	RIM	RPM
Diamond Blade	22.2mm	3.2mm	Segmented	5000

9.5 kg
21 lbs



CYCLONE

097-0001


MAGNETIC SHAVING COLLECTOR

Easily Picks up Steel Shavings and other Ferrous workshop debris

- Rubber grip handle
- Maximum lifting weight: 6.5 kg

0.5 kg

Simply slide the plunger and the shavings are neatly deposited.



TWISTER

UK 110v: 013-0002, UK 230v: 013-0001, EU 230v: 013-0003

1100W VARIABLE SPEED MIXER

SUPPLIED WITH MIXING PADDLE

- Variable Speed Control: 250-750min-1
- Vibration Data: 0.5-0.7m/s²
- Ergonomic Soft Grip Handle
- No More Manual Mixing
- 2 Years Limited Warranty

MIX:

Plaster, Mortar & Cement.
Ideal for all Popular Mixing Applications

4.9 kg
10.8 lbs

Twister Paddle Available: 013-0006

