




Reed Switch - Sub-Micro - Normally Open Contacts Part Number : ORD211 **Product Data Sheet**

PICTURE

DIMENSIONS



All dimensions in mm (inches) nominal.

✓ RoHS Compliant

SPECIFICATION Contact Form Normally Open **Contact Material** Rhodium 1 VA Switching Capacity Max. 24 VAC/DC Switching Voltage Max. Switching Current Max. 0.1 A Carrying Current Max. 0.3 A 150 VDC **Dielectric Strength** Min. 100 mOhms Contact Resistance Max. 10[°] Insulation Resistance Min. Pull - In - Sensitivity 10 - 40 AT Min. Drop - Out - Sensitivity 5 Max. **Bounce Time** 0.3 ms Max. **Release Time** 0.05 ms Тур. **Resonant Frequency** 7500 Hz Max. **Operating Frequency** 500 Hz Vibration (10-1000Hz) 20 g Shock (11 ms) 30 Тур. 0.2pF Capacitance -40°C + 125°C **Operating Temperature Range** Test Coil Туре 0211

NOTE

 When cutting or bending switch leads it is important that the glass seal is not damaged. The cutting or bending point should be no closer than 3mm (.118in.) to the glass to metal seal and the lead should be supported between the cutting or bending point and the glass to metal seal.

We offer a crop and form service for Reed Switches to be customized to your specification.



Ordering Information

PART NUMBER ORD211 10

- Type _
- <u>40</u>
- Minimum (AT) Sensitivity Maximum (AT)
- Sensitivity

Example:

Type ORD211 Standard Sensitivity. Pull-in sensitivity between 10-40 AT is PART NO: ORD211 10 40 Available in ranges of 5 AT e.g: 10-15, 15-20 etc.

Rev. No.	Revision Note	Date	Signature
2	Datasheet Redesign	08-06-06	NG

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to CERTIFIED BY help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied STR-R to our standard conditions of sale unless otherwise agreed in writing. ISO 9001: 2000 Fax: (1) 973 777 8405

Phone: (1) 973 777 6900 www.comus-intl.com

©2006 Copyright Comus International Ltd, 454 Allwood Road, Clifton, New Jersey, 07012, USA.