

## Screw tap, HSSE M ISO 2 (6H) 15° (right) 371 C

for use in non-ferrous metals

**ATORN®**



### Application

For producing metric threads on CNC or conventional machines in **through holes** in the non-ferrous metals material group.

### Version

- structural dimensions in accordance with: DIN 371 = reinforced shank (up to M10), DIN 376 = over-long shank (from M12)

### Advantage

- innovative cutting geometry with interrupted thread reduces torque, improves lubricant distribution and ensures extremely good process reliability and chip removal
- specialised application with optimised chip geometry, for use in non-ferrous metals with adhesive or lubricating properties

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	16					18	18	15	18	15	15	13							

<b>Art. No.</b>	<b>13254 030</b>
<b>Type</b>	M MAX Control
<b>Thread type</b>	Metric thread
<b>Thread type x nominal diameter</b>	M3
<b>Pitch</b>	0.5 mm
<b>Hole type</b>	Blind hole ≤ 2.5xD
<b>Cutting material</b>	HSSE
<b>Surface</b>	Uncoated
<b>Lead angle shape</b>	C
<b>Tolerance of screw taps</b>	ISO 2 (6H)
<b>Twist angle</b>	15° (right)
<b>Shaft diameter</b>	3.5 mm
<b>Application type/machine type</b>	CNC, Conventional
<b>Core hole diameter</b>	2.5 mm
<b>Coolant supply</b>	External
<b>Length</b>	56 mm
<b>Shank square</b>	2.7 mm
<b>Cutting speed (steel 1000) suitability</b>	3
<b>Cutting speed (steel 1300) suitability</b>	3
<b>Overall stainless steel suitability</b>	3
<b>fitness not iron total</b>	1
<b>fitness Titan/Nickel/Super total</b>	3
<b>Cutting speed (cast) suitability</b>	3
<b>Cutting speed (hard 55) suitability</b>	3
<b>Cutting speed (hard 65) suitability</b>	3
<b>DIN</b>	371

### EAN-Code

4050293189575