

Miniature cutting insert, type AG HC5640

For internal recessing

ATORN[®]



Application

For internal recessing in the material groups steel and (stainless steel) at low to high cutting speeds and under average cutting conditions.

Version

- Solid carbide cutting insert with internal cooling

Advantage

- Tough cemented carbide grade for a broad scope of application
- Stable geometry for the cutting insert
- Ideal for use with low-performance machines and unstable cutting conditions

Art. No.	17129 232
ISO name	AG
Shaft diameter	6 mm
Length	51 mm
Clearance length	15 mm
Programming size 2	1.4 mm
Recessing width	1 mm
Programming size	2.8 mm
Min. bore diameter	6.1 mm
Machining direction	Left
Carbide type	HC5640
Material to be processed	Steel, Stainless steel, Non-ferrous metal, Cast metal

EAN-Code

4050293266948