















THIS DRAWING IS A CONTROLLED DOCUMENT. DWG NO. 1583004

TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 						CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.
							LOOSE PIECE 			STRIP FORM 				
91505-1	0.2 - 0.6 [24-20]	1.14 - 1.78 [.045-.070]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.01 ± 0.05 [.039 ± .002]	66103-[] 66400-[] 164163-[]	66105-[] 163086-[]	66399-[] 163088-[] 170246-[] 170248-[] 66702-[]	66102-[] 66332-[] 164160-[]	66104-[] 163085-[]	66331-[] 163087-[] 170245-[] 170247-[]	Type III+ (yellow)	114-10004
91505-3	0.8 - 1.4 [18-16]	2.03 - 2.54 [.080-.100]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.30 ± 0.05 [.051 ± .002]	66099-[] 164164-[] 66589-[]	66101-[] 163082-[] 164839-[] 170244-[] 66590-[]	163084-[] 164840-[] 170242-[]	66098-[] 164161-[] 66579-[]	66100-[] 163081-[] 163766-[] 170243-[] 66580-[]	163083-[] 163767-[] 170241-[]	Type III+ (blue and violet)	114-10004
91515-1	0.05 - 0.38 [30-22]	1.02-1.91 [.040-.075]	NO	NO	3.50-4.75 [.140-.187]	0.79 ± 0.05 [.031 ± .002]	61173-[]	61174-[]	350078-[]	350079-[]	COMMERCIAL M-N-L		114-1012	
91515-3	0.08 - 0.24 [28-24]	0.89-1.40 [.035-.055]					66107-[] 163092-[] 66595-[]	66109-[] 164163-[] 66596-[]	163090-[] 170250-[] 170252-[]	66106-[] 163091-[] 66585-[]	66108-[] 164160-[] 66586-[]	163089-[] 170249-[] 170251-[]	Type III+ (red)	114-10004
91515-3	0.2 - 0.6 [24-20] 0.05 - 0.15 [30-26]	1.14-1.78 [.045-.070]					66103-[] 163088-[] 66428-[] 66593-[]	66105-[] 164162-[] 66429-[] 66594-[]	163086-[] 170246-[] 170248-[]	66102-[] 163087-[] 66424-[] 66583-[]	66104-[] 164159-[] 66425-[] 66584-[]	163085-[] 170245-[] 170247-[]	Type III+ (yellow & brown)	114-10004
91519-1	0.8 - 1.4 [18-16]	2.03-2.54 [.080-.100]	YES	NO	3.96 ± 0.38 [.156 ± .015]	1.30 ± 0.05 [.051 ± .002]	66360-[] 66361-[]			66358-[] 66359-[]		Type III+	114-10004	
91519-3	1.9 - 2.1 [14]						1.73 ± 0.05 [.068 ± .002]	66601-[] 66602-[]			66598-[] 66597-[]		Type III+	114-10004
91521-1	0.8 - 1.4 [18-16]	2.79-3.81 [.110-.150]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.30 ± 0.05 [.051 ± .002]	213603-2 213603-4			213603-1 213603-3		Type III+	114-10004	
91521-3	1.9 - 2.1 [14]						1.73 ± 0.05 [.068 ± .002]	66400-[] 66399-[]			66332-[] 66331-[]		Type III+ (yellow)	114-10004
91523-1	0.2 - 0.6 [24-20]	2.03-2.54 [.080-.100]	NO	NO	3.56-4.75 [.140-.187]	0.99 ± 0.05 [.039 ± .002]	163082-[]	164164-[]	66101-[]	163081-[]	164161-[]	66100-[]	Type III+ (blue)	114-10004
91523-3	0.8 - 1.4 [18-16]						1.30 ± 0.05 [.051 ± .002]	163084-[]	66099-[]	170242-[]	163083-[]	66098-[]	170243-[]	66579-[]
91542-1	0.2 - 0.35 [24-22]	1.52-3.43 [.060-.135]	YES	NO	3.96 ± 0.38 [.156 ± .015]	0.89 ± 0.08 [.035 ± .003]	66565-[] 66566-[]			66563-[] 66564-[]		Type III+ (yellow)	114-10004	
91542-3	2X 0.2 DR 0.56 [2X 24 DR 20]						0.99 ± 0.08 [.039 ± .003]	66587-[] 66588-[]			66577-[] 66578-[]		Type VI	114-10007
91550-1	0.8 - 1.4 [18-16]	2.03-3.43 [.080-.135]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.30 ± 0.05 [.051 ± .002]	66587-[] 66588-[]			66577-[] 66578-[]		Type VI	114-10007	
91550-3	1.9 - 2.1 [14]						1.73 ± 0.05 [.068 ± .002]							

 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

- 2. AMP and CERTI-CRIMP are trademarks.
-  -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
- 4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWN: M. YOUNGER 21FEB2012		MATERIAL: -		HEAT TREAT: -	
CHK: B.A. WOLFE 22FEB2012		APVD: B.A. WOLFE 22FEB2012		 TE Connectivity	
NAME: B.A. WOLFE		SCALE: -			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SURFACE TEXTURE: 	
0 PLC ± -		1 PLC ± -		2 PLC ± -	
3 PLC ± -		4 PLC ± -		SCALE: -	
P LTR		REVISION RECORD		DATE: 09/2015	
D REVISED		AW BAW		DRAWING NO: 1583004	
P LTR		REVISION RECORD		SHEET: 1 of 2	

LOC: A
DIST: 00

TOOL NUMBER	WIRE SIZE mm ² [AWG]	INSULATION DIAMETER mm [in.]	INSUL. ADJ.	FLIP LOCATOR	STRIP LENGTH mm [in.]	CRIMP HEIGHT mm [in.]	CONTACT PART NUMBERS ¹		CONTACT DESCRIPTION (loose piece color code)	APPLIC. SPECIF.				
							LOOSE PIECE	STRIP FORM						
91564-1 91564-3	0.20-0.56 [24-20]	1.02-2.03 [.040-.080]	NO	NO	3.55-4.75 [.140-.187]	1.00 ± 0.05 [.039 ± .002]	66103-[]	66593-[]	66596-[]	66102-[]	66583-[]	66586-[]	Type III+ (yellow) (red)	114-10004
	0.05-0.15 [30-26]	1.02-1.52 [.040-.060]					66105-[]	170246-[]	66594-[]	66104-[]	170245-[]	66584-[]		
	0.12-0.22 [26-24]	0.89-1.40 [.035-.055]					66107-[]	66237-[]	170252-[]	66106-[]	170249-[]	66108-[]		

- ¹ LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.
2. AMP and CERTI-CRIMP are trademarks.
- ³ -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWN	M. YOUNGER	21FEB2012	MATERIAL	-	HEAT TREAT	-					
CHK	B.A.WOLFE	22FEB2012	TE Connectivity								
APVD	B.A. WOLFE	22FEB2012									
NAME	B.A. WOLFE										
CERTI-CRIMP II TOOL DATA SHEET MULTIMATE CONTACT FAMILY OPEN BARREL											
SCALE	-	SIZE	A1	DRAWING NO	1583004	SHEET	2	OF	2	REV	D

DIMENSIONS:	mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC	± .	± .
1 PLC	± .	± .
2 PLC	± .	± .
3 PLC	± .	± .
4 PLC	± .	± .
ANGLES#	-	
SURFACE TEXTURE	√	

P	LTR	REVISION RECORD	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

LOC
A
DIST
00

THIS DRAWING IS A CONTROLLED DOCUMENT. DRAW NO 1583004

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE. IT IS THE PROPERTY OF TE CONNECTIVITY AND IS NOT TO BE DISCLOSED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN AUTHORIZATION OF TE. © 2011 TE CONNECTIVITY