

## UNITRONIC® LiYY (TP)

Data transmission cable with colour code acc. to DIN 47100 and twisted pairs

UNITRONIC® LiYY (TP): Low-frequency PVC data cable DIN 47100 coded, Flexible, 0.34mm<sup>2</sup> Maxi TERMI-POINT®, Twisted Pairs, Flame retardant, Instrumentation Control

### Info

TP = twisted pair

CPR: Article number choice under [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



### Benefits

Decoupling of circuits by means of twisted-pair (TP) design (crosstalk effects)

### Application range

Electronic devices tend to leave little room for installing cables, meaning short travel distances and small bending radii are required. This cable ideally meets these requirements.

Dry or damp rooms

### Product features

Twisted in pairs to reduce decoupling. As a result, additional screening is often not required.

Flame-retardant according IEC 60332-1-2

### Norm references / Approvals

Based on VDE 0812

### Product Make-up

Fine-wire strand made of bare copper wires

Core insulation made of PVC

TP structure

Outer sheath made of PVC

Outer sheath colour: pebble grey (RAL 7032)

Last Update (20.01.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## UNITRONIC® LiYY (TP)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	DIN 47100, refer to Appendix T9
Mutual capacitance:	Approx. 120 nF/km
Inductivity:	approx. 0.65 mH/km
Conductor stranding:	Fine copper wire strands
Minimum bending radius:	Occasional flexing: 10 x outer diameter Fixed installation: 4 x Outer diameter
Temperature range:	Occasional flexing: -5°C to +70°C Fixed installation: -40°C to +80°C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil  $\leq$  30 kg or  $\leq$  250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**UNITRONIC® LiYY (TP)**

Article number	Number of pairs and conductor cross section (mm <sup>2</sup> )	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
UNITRONIC® LiYY (TP)				
0035101	2 x 2 x 0.14	4.5	5.4	25.5
0035102	3 x 2 x 0.14	5	8	32
0035103	4 x 2 x 0.14	5.6	10.7	38.5
0035104	5 x 2 x 0.14	5.8	13.4	45.5
0035105	6 x 2 x 0.14	6.3	16.1	51
0035108	10 x 2 x 0.14	8.1	26.9	77.5
0035110	12 x 2 x 0.14	8.3	32.3	94.5
0035113	16 x 2 x 0.14	9.2	43	110.5
0035160	2 x 2 x 0.25	5.7	9.6	38
0035161	3 x 2 x 0.25	6.3	14.4	48
0035162	4 x 2 x 0.25	7	19.2	59
0035163	6 x 2 x 0.25	7.9	28.8	80
0035164	8 x 2 x 0.25	9.3	38.4	98
0035170	2 x 2 x 0.5	7.3	19.2	72
0035171	3 x 2 x 0.5	8.1	28.8	83
0035172	4 x 2 x 0.5	8.8	38.4	115
0035174	8 x 2 x 0.5	12.3	76.8	206
0035175	10 x 2 x 0.5	13.3	96	247

Last Update (20.01.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet:  
PN 0456 / 02\_03\_16