

# HERKULES

MITLAUFENDES AUFFANGSYSTEM UND MOBILES HORIZONTALES SEILSYSTEM

GUIDED TYPE FALL ARRESTER SYSTEM AND MOBILE HORIZONTAL ROPE SYSTEM

NEW!

## ➤ BESCHREIBUNG

Zusätzlich zu den klassischen Anwendungen eines mitlaufenden Auffangsystems (wie FOSSY, LORY, EDGER) kann das HERKULES auch zwischen zwei Anschlagpunkten gespannt und somit als mobiles horizontales Seilssystem verwendet werden. Dieses zusätzliche Feature steigert die Arbeitseffizienz, weil größere Arbeitsbereiche abgesichert werden können.

Das HERKULES System eignet sich durch seine einfache Ausführung speziell für kurzfristige Tätigkeiten bei denen schnell und flexible eine benutzerfreundliche Anschlageinrichtung benötigt wird.

## ➤ AUSSTATTUNG

12 mm Kernmantelseil mit Schutzschlauch  
Auffanggerät HERKULES Bandfalldämpfer mit textiler Hülle und BSK Schraubkarabiner  
AHK Einhandkarabiner  
Abnehmbare Nahtschutzhülse an beiden Enden

## ➤ TECHNISCHE DATEN

Norm: EN 358, EN 353-2, EN 795B, CEN/TS 16415 TYP C  
Gewicht: 1 / 1,2 / 1,3 / 1,7 / 2,3 / 2,8 kg  
Material: 12 mm Kernmantelseil  
Farbe: Orange / schwarz  
Kunststoff: PA Polyamid  
Beschlüge: Aluminium, Stahl  
Längen: : 3 / 5 / 10 / 15 m  
Temperatur: -35 °C bis 40 °C

## ➤ MOBILES HORIZONTALES SEILSYSTEM

Norm: EN 795B, CEN/TS 16415 TYP C  
max. Anzahl der Benutzer: 2 (max. 1 pro Spannfeld)  
max. Feldbreite: 12 m  
min. Feldbreite: 4 m  
max. Seilaußenlenkung: 2 m

## ➤ DESCRIPTION

In addition to the classic applications of a guided type fall arrester system such as FOSSY, LORY, EDGER), HERKULES can also be stretched between two anchor points to be used as a mobile horizontal rope system.

This additional feature increases work efficiency, because larger working areas can be secured. Thanks to its simple design, the HERKULES system is particularly suitable for short-term activities requiring a user-friendly, quick and flexible anchor device.

## ➤ EQUIPMENT

12 mm kernmantle rope with protective tube,  
fall arrester HERKULES,  
tape fall absorber with textile cover and BSK screw karabiner,  
AHK one-hand karabiner,  
detachable protective sleeve for the seams on both ends

## ➤ TECHNICAL DATA

Standard: EN 358, EN 353-2, EN 795B, CEN/TS 16415 TYPE C  
Weight: 1 / 1.2 / 1.3 / 1.7 / 2.3 / 2.8 kg  
Material: 12 mm kernmantle rope  
Colour: orange / black  
Synthetic material: PA polyamide  
Fittings: aluminium, steel  
Lengths: : 3 / 5 / 10 / 15 m  
Temperature: -35 °C to 40 °C

## ➤ MOBILE HORIZONTAL ROPE SYSTEM

Standard: EN 795B, CEN/TS 16415 TYPE C  
max. number of users: 2 (max. 1 per span)  
max. field width: 12 m  
min. field width: 4 m  
max. rope deflection: 2 m



Praxisanwendung aus dem Fotoshooting für diesen Katalog.  
Practical application from the photo shooting for this catalogue.

## PRODUKT / PRODUCT

Herkules	3 m	800524
	5 m	800525
	10 m	800526
	15 m	800527
	20 m	800567
	25 m	800541