

Pneumatic ratchet screwdriver MDR 2102

**MANNESMANN
DEMAG**

Application:

Compact for use in confined spaces

Art. no.	75061 210
Model	MDR 2102
Oil-free operation	No
Suitable for screw	M10
Max. tightening torque	160 Nm
Max. idle speed	180 rpm
Max. torque	160 Nm
Air consumption	10.8 l/s
Tool holding device	1/2-inch external square
Connection thread	1/4 inch
Inner hose diameter	10 mm
Sound-pressure level	84
Valve design	Lever valve
Length	270 mm
Weight	1.3 kg
With right/left-hand rotation	Yes



EAN-Code

4251757302725