

Thermistor motor protection relay Standard evaluation unit 22.5 mm enclosure screw terminal 2 change-over contacts US = 24 V AC/DC Manul/Remote-Reset with ATEX approval 2 LEDs (READY/TRIPPED) galvanic isolation Test/reset button Wire break monitoring Short circuit monitoring



Product brand name	SIRIUS
Product category	SIRIUS 3RN2 thermistor motor protection
Product designation	Thermistor motor protection relay
Design of the product	Standard evaluation unit with ATEX approval, open-circuit and short-circuit detection in the sensor circuit
Product type designation	3RN2

General technical data	
Display version LED	Yes
Power loss [W] for rated value of the current	
• at AC in hot operating state	1.2 W
• at DC in hot operating state	1.2 W
Degree of pollution	3
Surge voltage resistance rated value	4 kV
Protection class IP	IP20
Shock resistance	
• acc. to IEC 60068-2-27	11g / 15 ms
Mechanical service life (switching cycles)	
• typical	10 000 000
Electrical endurance (switching cycles)	

<ul style="list-style-type: none"> • at AC-15 at 230 V typical 	100 000
Thermal current of the switching element with contacts maximum	5 A
Reference code acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750	K
Reference code acc. to DIN EN 81346-2	K
Reference code acc. to DIN EN 61346-2	K

Control circuit/ Control	
Type of voltage of the control supply voltage	AC/DC
Control supply voltage at AC	
<ul style="list-style-type: none"> • at 50 Hz rated value • at 60 Hz rated value 	24 ... 24 V
Control supply voltage at DC	
<ul style="list-style-type: none"> • rated value 	24 ... 24 V
Operating range factor control supply voltage rated value at DC	
<ul style="list-style-type: none"> • initial value • Full-scale value 	0.85
Operating range factor control supply voltage rated value at AC at 50 Hz	
<ul style="list-style-type: none"> • initial value • Full-scale value 	0.85
Operating range factor control supply voltage rated value at AC at 60 Hz	
<ul style="list-style-type: none"> • initial value • Full-scale value 	0.85
Inrush current peak	
<ul style="list-style-type: none"> • at 24 V 	0.5 A
Duration of inrush current peak	
<ul style="list-style-type: none"> • at 24 V 	50 ms

Measuring circuit	
Buffering time in the event of power failure minimum	40 ms

Precision	
Relative metering precision	2 %

Auxiliary circuit	
Material of switching contacts	AgSnO2
Number of NC contacts for auxiliary contacts	0
Number of NO contacts for auxiliary contacts	0
Number of CO contacts	
<ul style="list-style-type: none"> • for auxiliary contacts 	2
Operating current of auxiliary contacts at DC-13	
<ul style="list-style-type: none"> • at 24 V 	1 A

- at 125 V 0.2 A
- at 250 V 0.1 A

Main circuit

Operating frequency rated value 50 ... 60 Hz

Outputs

Ampacity of the output relay at AC-15

- at 250 V at 50/60 Hz 3 A

Ampacity of the output relay at DC-13

- at 24 V 1 A
- at 125 V 0.2 A

Continuous current of the DIAZED fuse link of the output relay

6 A

Electromagnetic compatibility

Conducted interference

- due to burst acc. to IEC 61000-4-4 2 kV (power ports) / 1 kV (signal ports)
- due to conductor-earth surge acc. to IEC 61000-4-5 2 kV (line to ground)
- due to conductor-conductor surge acc. to IEC 61000-4-5 1 kV (line to line)

Electrostatic discharge acc. to IEC 61000-4-2

6 kV contact discharge / 8 kV air discharge

Galvanic isolation

Design of the electrical isolation galvanic isolation

Galvanic isolation

- between entrance and outlet Yes
- between the outputs Yes
- between the voltage supply and other circuits No

Safety related data

Safety Integrity Level (SIL) acc. to IEC 61508 1

Safe failure fraction (SFF) 74 %

Failure rate [FIT]

- at rate of recognizable hazardous failures (λ_{dd}) 0.000000068 1/h
- at rate of non-recognizable hazardous failures (λ_{du}) 0.000000031 1/h

PFHD with high demand rate acc. to EN 62061 0.00000038 1/h

PFDAvg with low demand rate acc. to IEC 61508 0.0041

MTBF 97 y

MTTFd 303 y

Hardware fault tolerance acc. to IEC 61508 0

T1 value for proof test interval or service life acc. to IEC 61508 3 y

Connections/ Terminals

Product function	
<ul style="list-style-type: none"> removable terminal for auxiliary and control circuit 	Yes
Type of electrical connection	
<ul style="list-style-type: none"> for auxiliary and control current circuit 	screw-type terminals screw-type terminals
Type of connectable conductor cross-sections	
<ul style="list-style-type: none"> solid 	1x (0.5 ... 4.0 mm ²), 2x (0.5 ... 2.5 mm ²)
<ul style="list-style-type: none"> finely stranded with core end processing 	1x (0.5 ... 4 mm ²), 2x (0.5 ... 1.5 mm ²)
<ul style="list-style-type: none"> at AWG conductors solid 	1x (20 ... 12), 2x (20 ... 14)
Connectable conductor cross-section	
<ul style="list-style-type: none"> solid 	0.5 ... 4 mm ²
<ul style="list-style-type: none"> finely stranded with core end processing 	0.5 ... 4 mm ²
AWG number as coded connectable conductor cross section	
<ul style="list-style-type: none"> solid 	20 ... 12
<ul style="list-style-type: none"> stranded 	20 ... 12
Tightening torque	
<ul style="list-style-type: none"> with screw-type terminals 	0.6 ... 0.8 N·m

Installation/ mounting/ dimensions

Mounting position	any
Mounting type	screw and snap-on mounting onto 35 mm standard mounting rail
Height	100 mm
Width	22.5 mm
Depth	90 mm
Required spacing	
<ul style="list-style-type: none"> with side-by-side mounting <ul style="list-style-type: none"> — forwards — Backwards — upwards — downwards — at the side 	0 mm 0 mm 0 mm 0 mm 0 mm
<ul style="list-style-type: none"> for grounded parts <ul style="list-style-type: none"> — forwards — Backwards — upwards — at the side — downwards 	0 mm 0 mm 0 mm 0 mm 0 mm
<ul style="list-style-type: none"> for live parts <ul style="list-style-type: none"> — forwards — Backwards — upwards — downwards 	0 mm 0 mm 0 mm 0 mm

— at the side

0 mm

Ambient conditions

Installation altitude at height above sea level <ul style="list-style-type: none">• maximum	2 000 m
Relative humidity <ul style="list-style-type: none">• during operation	70 %
Explosion protection category for dust	[Ex t] [Ex p]
Explosion protection category for gas	[Ex e] [Ex d] [Ex px]

Certificates/ approvals

General Product Approval	EMC	For use in hazardous locations
---------------------------------	------------	---------------------------------------



Declaration of Conformity	Test Certificates	Marine / Shipping
----------------------------------	--------------------------	--------------------------



EG-Konf.

[Miscellaneous](#)

[Type Test Certificates/Test Report](#)



LRS



PRS



DNVGL.COM/AF

other

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

www.siemens.com/sirius/catalogs

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RN2011-1BA30>

Cax online generator





<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RN2011-1BA30>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RN2011-1BA30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RN2011-1BA30&lang=en





last modified:

07/26/2019