

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 32_TNC-50-0-1/133_N

Rev.: A 

Description

Adaptor plug/plug

Interface standards
IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz
Frequency range	DC to 11 GHz
Return loss	≥ dB

Mechanical Data

Weight	0.0278 kg
--------	-----------

Environmental Data

Operating Temperature 2002/95/EC (RoHS)	-65 °C to 165 °C compliant
--	-------------------------------

Material Data

Piece Parts

Piece Parts	Material
Centre contact	Brass
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE
Coupling nut	Brass
Gasket	MVQ (Silicone Rubber)

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00013697
Catalogue drawing	DCA-00013699

Ordering Information

Single package	32_TNC-50-0-1/133_NE
----------------	----------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions