



Model Number

NBN3-F31K2M-Z8L-B13-S

Features

- Direct mounting on standard actuators
- Compatible with all process control systems
- Weatherproof housing for outdoor applications
- Rugged metal base
- Temperature range -40 ... 167 °F (-40°C to 75°C)
- 2-wire DC sensor with minimum off-state current
- LEDs for switching state of sensor and solenoid valve
- Plug-in terminals

Application

Note

The connections to this sensor are sealed with stopping plugs to protect against dirt and moisture. If not all of the connections are used in your application, then seal the remaining stopping plugs on the sensor permanently or check during initial installation and when performing regular maintenance work that the stopping plugs are secure and impermeable. If necessary, tighten the stopping plugs to a torque of 1 Nm.

Accessories

BT65-F31K2-RG-EN
Activator for F31K2 series

BT65A
Activator for F31 series

BT65X
Activator for F31 series

Technical Data

General specifications

Switching function	2 x normally open (NO)
Output type	Two-wire
Rated operating distance	s_n 2.5 mm
Installation	for non-flush mounting
Output polarity	DC
Assured operating distance	s_a 0 ... 2.05 mm
Output type	2x 2-wire

Nominal ratings

Operating voltage	U_B	6 ... 30 V
Switching frequency	f	0 ... 100 Hz
Hysteresis	H	typ. 0.5 mm
Reverse polarity protection		reverse polarity tolerant
Short-circuit protection		no
Voltage drop	U_d	≤ 6 V
Operating current	I_L	4 ... 100 mA
Off-state current	I_r	100 ... 200 μA typ. 160 μA
Switching state indicator		LED, yellow
Valve status indicator		LED, yellow

Functional safety related parameters

MTTF _d	684 a
Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	0 %

Electrical specifications

Connection	Valve circuit
Power	voltage: 10 ... 32 V current: max. 240 mA

Ambient conditions

Ambient temperature	-40 ... 75 °C (-40 ... 167 °F), restriction for use in hazardous area, see instruction manual
Storage temperature	-40 ... 85 °C (-40 ... 185 °F)

Mechanical specifications

Connection (system side)	screw terminal, M20 x 1.5 cable gland
Core cross-section (system side)	1.5/2.5 mm ² flexible/rigid
Connection (valve side)	screw terminal, Cable gland M20 x 1.5
Housing material	rugged, translucent polycarbonate (PC) optimised for outdoor use
Housing base	powder coated aluminum
Degree of protection	IP66 / IP67 / IP69K
Tightening torque, housing screws	≤ 2 Nm
Tightening torque, cable gland	≤ 4 Nm
Tightening torque, stopping plug	1 Nm


Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007 VDI / VDE 3845

Approvals and certificates

EAC conformity	TR CU 020/2011
----------------	----------------

Dimensions



Electrical Connection

